

# DATA SHEET

## O-Ring 106699

### PART INFORMATION

|                                       |             |
|---------------------------------------|-------------|
| Part number                           | 106699      |
| Inside diameter d1                    | 6,07 mm     |
| Cross-section d2                      | 1,78 mm     |
| Size standard                         | BS010/AS010 |
| Tolerance range according to          | ISO 3601-1  |
| Rubber family                         | EPDM        |
| Rubber compound                       | EP856       |
| Quality acceptance criteria on aspect | ISO 3601-3  |



### EP856 COMPOUND INFORMATION

#### Original characteristics

|                                 |                  |
|---------------------------------|------------------|
| Hardness Sh A                   | 80               |
| Tensile strength                | 16 MPa           |
| Elongation at break             | 160 %            |
| Compression set                 | 15 % (24h 150°C) |
| TR10                            | -46 °C           |
| Brittle point                   | -55 °C           |
| Operational temperature range * | -50 °C / 140 °C  |
| Peak temperature                | 175 °C           |

Rubber color                      Black

#### Official agreements

Food : FR, USA  
Potable water : DE, FR, GB

### EPDM FAMILY

#### Very good resistance

Water, steam and water-based solutions  
Synthetic brake fluids  
Atmospheric agents  
Low temperature

#### Poor resistance

Mineral oils and hydrocarbons

#### Particularities

Fairly good mechanical behaviour

#### Typical applications

Hot and cold water taps  
Drinking water  
SF6 circuit breakers  
Cooling circuit  
Brake circuit  
Heating circuit

\* The temperature range is given as an indication and can be influenced by the environment, the fluids in contact and the operating conditions.

