



Main

| | |
|-----------------------------|--|
| Circuit breaker application | Distribution |
| Range of product | IC60 |
| Device short name | IC60N |
| Poles description | 2P |
| Number of protected poles | 2 |
| [In] rated current | 3 A |
| Network type | AC DC |
| Trip unit technology | Thermal-magnetic |
| Curve code | C |
| Utilisation category | Category A EN 60947-2 Category A IEC 60947-2 |
| Suitability for isolation | Yes EN 60898-1 Yes EN 60947-2 Yes IEC 60898-1 Yes IEC 60947-2 |

Complementary

| | |
|---------------------------------------|---|
| Network frequency | 50/60 Hz |
| [Ue] rated operational voltage | 100...130 V AC 50/60 Hz 12...60 V AC 50/60 Hz 220...240 V AC 50/60 Hz 380...415 V AC 50/60 Hz 400 V AC 50/60 Hz 440 V AC 50/60 Hz 12...144 V DC |
| Magnetic tripping limit | 8 x In +/- 20 % |
| Breaking capacity | 50 kA Icu EN 60947-2 100...130 V AC 50/60 Hz 50 kA Icu EN 60947-2 12...60 V AC 50/60 Hz 50 kA Icu EN 60947-2 220...240 V AC 50/60 Hz 50 kA Icu EN 60947-2 380...415 V AC 50/60 Hz 50 kA Icu IEC 60947-2 100...130 V AC 50/60 Hz 50 kA Icu IEC 60947-2 12...60 V AC 50/60 Hz 50 kA Icu IEC 60947-2 220...240 V AC 50/60 Hz 50 kA Icu IEC 60947-2 380...415 V AC 50/60 Hz 6000 A Icn EN 60898-1 400 V AC 50/60 Hz 6000 A Icn IEC 60898-1 400 V AC 50/60 Hz 25 kA Icu EN 60947-2 440 V AC 50/60 Hz 25 kA Icu IEC 60947-2 440 V AC 50/60 Hz 6 kA Icu EN 60947-2 12...144 V DC 6 kA Icu IEC 60947-2 12...144 V DC |
| [Ics] rated service breaking capacity | 50 kA 100 % EN 60947-2 100...130 V AC 50/60 Hz 50 kA 100 % EN 60947-2 12...60 V AC 50/60 Hz 50 kA 100 % EN 60947-2 220...240 V AC 50/60 Hz 50 kA 100 % IEC 60947-2 100...130 V AC 50/60 Hz 50 kA 100 % IEC 60947-2 12...60 V AC 50/60 Hz 50 kA 100 % IEC 60947-2 220...240 V AC 50/60 Hz 6 kA 100 % EN 60947-2 12...144 V DC 50 kA 100 % EN 60947-2 380...415 V AC 50/60 Hz 25 kA 100 % EN 60947-2 440 V AC 50/60 Hz 6 kA 100 % IEC 60947-2 12...144 V DC 50 kA 100 % IEC 60947-2 380...415 V AC 50/60 Hz 25 kA 100 % IEC 60947-2 440 V AC 50/60 Hz |
| Limitation class | 3 EN 60898-1 3 IEC 60898-1 |
| [Ui] rated insulation voltage | 500 V AC 50/60 Hz EN 60947-2 500 V AC 50/60 Hz IEC 60947-2 |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

| | |
|--|---|
| [Uimp] rated impulse withstand voltage | 6 kV EN 60947-2 6 kV IEC 60947-2 |
| Contact position indicator | Yes |
| Control type | Toggle |
| Local signalling | Trip indicator |
| Mounting mode | Removable comb busbar installed |
| Mounting support | DIN rail |
| 9 mm pitches | 4 |
| Width | 36 mm |
| Colour | White |
| Connections - terminals | Tunnel terminal with flap top or bottom 1...25 mm ² solid 1 Tunnel terminal with flap top or bottom 0.5...16 mm ² flexible with cable end 1 Tunnel terminal with flap top or bottom 0.5...16 mm ² flexible without cable end 1 Tunnel terminal with flap top or bottom 1.5 mm ² flexible without cable end 1...5 Tunnel terminal with flap top or bottom 1.5 mm ² solid 1...5 Tunnel terminal with flap top or bottom 2.5 mm ² flexible without cable end 1...3 Tunnel terminal with flap top or bottom 2.5 mm ² solid 1...3 |
| Wire stripping length | 14 mm top or bottom |
| Tightening torque | 2 nm top or bottom |
| Earth-leakage protection | Separate block |

Environment

| | |
|---------------------------------------|--|
| Standards | EN 60898-1 EN 60947-2 IEC 60898-1 IEC 60947-2 |
| IP degree of protection | IP3 EN 60947-2 IP3 IEC 60947-2 |
| Pollution degree | 3 EN 60947-2 3 IEC 60947-2 |
| Electrical shock protection class | Class II front face |
| Tropicalisation | 2 EN/IEC 60068-2-78 |
| Relative humidity | 95 % |
| Operating altitude | 0...2000 m |
| Ambient air temperature for operation | -35...70 °C |
| Ambient air temperature for storage | -40...85 °C |
| RoHS EUR status | Compliant |
| RoHS EUR conformity date | 1001 |