



Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 11

LOCTITE SI 5980 known as Loctite 5980 200ml Es/Pt/It/Gr

SDS No. : 367607
V006.0

Revision: 20.02.2017
printing date: 27.09.2017

Replaces version from: 15.11.2016

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

LOCTITE SI 5980 known as Loctite 5980 200ml Es/Pt/It/Gr

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:
Silicone sealant

1.3. Details of the supplier of the safety data sheet

Henkel Ltd
Wood Lane End
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 1442 278000
Fax-no.: +44 1442 278071

ua-productsafety.uk@uk.henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Aerosols
H229 Pressurised container: May burst if heated.

Category 3

2.2. Label elements

Label elements (CLP):

Signal word: Warning

Hazard statement: H229 Pressurised container: May burst if heated.

Precautionary statement: P251 Do not pierce or burn, even after use.
P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources.
No smoking.

2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

SECTION 3: Composition/information on ingredients**3.2. Mixtures****Declaration of the ingredients according to CLP (EC) No 1272/2008:**

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Hexamethyldisilazane 999-97-3	213-668-5 01-2119438176-38	1- < 3 %	Flam. Liq. 2 H225 Acute Tox. 4; Oral H302 Acute Tox. 3; Dermal H311 Acute Tox. 4; Inhalation H332 Aquatic Chronic 3 H412
Trimethoxyvinylsilane 2768-02-7	220-449-8 01-2119513215-52	1- < 5 %	Flam. Liq. 3 H226 Acute Tox. 4; Inhalation H332

For full text of the H - statements and other abbreviations see section 16 "Other information".**Substances without classification may have community workplace exposure limits available.****SECTION 4: First aid measures****4.1. Description of first aid measures****Inhalation:**

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.

Obtain medical attention if irritation persists.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

Ingestion:

Rinse out mouth, drink 1-2 glasses of water, do not induce vomiting.

Seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

Prolonged or repeated contact may cause skin irritation.

Prolonged or repeated contact may cause eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

Carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons:

None known

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO₂) and nitrogen oxides (NO_x) can be released.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Avoid contact with skin and eyes.

Wear protective equipment.

Ensure adequate ventilation.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

For small spills wipe up with paper towel and place in container for disposal.

For large spills absorb onto inert absorbent material and place in sealed container for disposal.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Use only in well-ventilated areas.

Avoid skin and eye contact.

See advice in section 8

Hygiene measures:

Good industrial hygiene practices should be observed.

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

7.2. Conditions for safe storage, including any incompatibilities

Store only in the original container.

Refer to Technical Data Sheet

7.3. Specific end use(s)

Silicone sealant

SECTION 8: Exposure controls/personal protection

8.1. Control parameters**Occupational Exposure Limits**Valid for
Great Britain

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Limestone 1317-65-3 [CALCIUM CARBONATE, INHALABLE DUST]		10	Time Weighted Average (TWA):		EH40 WEL
Limestone 1317-65-3 [CALCIUM CARBONATE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		EH40 WEL
Limestone 1317-65-3 [LIMESTONE, RESPIRABLE MARBLE, RESPIRABLE]		4	Time Weighted Average (TWA):		EH40 WEL
Limestone 1317-65-3 [LIMESTONE, TOTAL INHALABLE MARBLE, TOTAL INHALABLE]		10	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [CALCIUM CARBONATE, INHALABLE DUST]		10	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [CALCIUM CARBONATE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [LIMESTONE, RESPIRABLE MARBLE, RESPIRABLE]		4	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [LIMESTONE, TOTAL INHALABLE MARBLE, TOTAL INHALABLE]		10	Time Weighted Average (TWA):		EH40 WEL

Occupational Exposure LimitsValid for
Ireland

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Limestone 1317-65-3 [CALCIUM CARBONATE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		IR_OEL
Limestone 1317-65-3 [CALCIUM CARBONATE, TOTAL INHALABLE DUST]		10	Time Weighted Average (TWA):		IR_OEL
Calcium carbonate 471-34-1 [CALCIUM CARBONATE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		IR_OEL
Calcium carbonate 471-34-1 [CALCIUM CARBONATE, TOTAL INHALABLE DUST]		10	Time Weighted Average (TWA):		IR_OEL

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Trimethoxyvinylsilane 2768-02-7	aqua (freshwater)		0,36 mg/l				
Trimethoxyvinylsilane 2768-02-7	aqua (marine water)		0,036 mg/l				
Trimethoxyvinylsilane 2768-02-7	aqua (intermittent releases)		2,4 mg/l				
Trimethoxyvinylsilane 2768-02-7	sewage treatment plant (STP)		6,6 mg/l				
Trimethoxyvinylsilane 2768-02-7	sediment (freshwater)				1,3 mg/kg		
Trimethoxyvinylsilane 2768-02-7	sediment (marine water)				0,13 mg/kg		
Trimethoxyvinylsilane 2768-02-7	soil				0,055 mg/kg		

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Trimethoxyvinylsilane 2768-02-7	Workers	dermal	Long term exposure - systemic effects		0,2 mg/kg	
Trimethoxyvinylsilane 2768-02-7	Workers	Inhalation	Long term exposure - systemic effects		2,6 mg/m ³	
Trimethoxyvinylsilane 2768-02-7	General population	dermal	Acute/short term exposure - systemic effects		0,1 mg/kg	
Trimethoxyvinylsilane 2768-02-7	General population	Inhalation	Acute/short term exposure - systemic effects		0,7 mg/m ³	
Trimethoxyvinylsilane 2768-02-7	General population	dermal	Long term exposure - systemic effects		0,1 mg/kg	
Trimethoxyvinylsilane 2768-02-7	General population	Inhalation	Long term exposure - systemic effects		0,7 mg/m ³	
Trimethoxyvinylsilane 2768-02-7	General population	oral	Long term exposure - systemic effects		0,1 mg/kg	
Trimethoxyvinylsilane 2768-02-7	Workers	dermal	Acute/short term exposure - systemic effects		0,2 mg/kg	
Trimethoxyvinylsilane 2768-02-7	Workers	Inhalation	Acute/short term exposure - systemic effects		2,6 mg/m ³	

Biological Exposure Indices:
None**8.2. Exposure controls:**

Engineering controls:
Ensure good ventilation/extraction.

Respiratory protection:

Use only in well-ventilated areas.

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A (EN 14387)

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; \geq 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; \geq 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.

Protective eye equipment should conform to EN166.

Skin protection:

Wear suitable protective clothing.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions.

Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	paste black
Odor	alcohol-like
Appearance	aerosol
Odour threshold	No data available / Not applicable
pH	Not determined
Initial boiling point	Not determined
Flash point	> 100,00 °C (> 212 °F)
Decomposition temperature	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Density	Not determined
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative)	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable

Oxidising properties

No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity**10.1. Reactivity**

None if used properly.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Stable under normal conditions of storage and use.

10.5. Incompatible materials

None if used properly.

10.6. Hazardous decomposition products

carbon oxides.

SECTION 11: Toxicological information**11.1. Information on toxicological effects****General toxicological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation (EC) No 1272/2008. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Oral toxicity:

May cause irritation to the digestive tract.

Inhalative toxicity:

Inhalation of vapors in high concentration may cause irritation of respiratory system

Skin irritation:

Prolonged or repeated contact may cause skin irritation.

Eye irritation:

Prolonged or repeated contact may cause eye irritation.

Acute oral toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Hexamethyldisilazane 999-97-3	LD50	851 mg/kg	oral		rat	OECD Guideline 401 (Acute Oral Toxicity)
Trimethoxyvinylsilane 2768-02-7	LD50	7.120 mg/kg	oral		rat	OECD Guideline 401 (Acute Oral Toxicity)

Acute inhalative toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Hexamethyldisilazane 999-97-3	Acute toxicity estimate (ATE)	10,1 mg/l	vapour			Expert judgement
Trimethoxyvinylsilane 2768-02-7	LC50	16,8 mg/l	Vapor.	4 h	rat	OECD Guideline 403 (Acute Inhalation Toxicity)

Acute dermal toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Hexamethyldisilazane 999-97-3	LD50	547 mg/kg	dermal		rat	OECD Guideline 402 (Acute Dermal Toxicity)
Trimethoxyvinylsilane 2768-02-7	LD50	3.540 mg/kg	dermal		rabbit	not specified

Germ cell mutagenicity:

Hazardous components CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Hexamethyldisilazane 999-97-3	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
	negative	mammalian cell gene mutation assay	with and without		OECD Guideline 476 (In vitro Mammalian Cell Gene Mutation Test)

SECTION 12: Ecological information**General ecological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation (EC) No 1272/2008. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

12.1. Toxicity**Ecotoxicity:**

Do not empty into drains / surface water / ground water.

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
Hexamethyldisilazane 999-97-3	LC50	88 mg/l	Fish	96 h	Brachydanio rerio (new name: Danio rerio)	OECD Guideline 203 (Fish, Acute Toxicity Test)
Hexamethyldisilazane 999-97-3	EC50	80 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Hexamethyldisilazane 999-97-3	NOEC	2,7 mg/l	Algae	72 h	Scenedesmus subspicatus (new name: Desmodesmus subspicatus)	OECD Guideline 201 (Alga, Growth Inhibition Test)
	EC50	19 mg/l	Algae	72 h	Scenedesmus subspicatus (new name: Desmodesmus subspicatus)	OECD Guideline 201 (Alga, Growth Inhibition Test)
Trimethoxyvinylsilane 2768-02-7	LC50	191 mg/l	Fish	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute Toxicity Test)
Trimethoxyvinylsilane 2768-02-7	EC50	> 100 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Trimethoxyvinylsilane 2768-02-7	EC50	> 100 mg/l	Algae	72 h		OECD Guideline 201 (Alga, Growth Inhibition Test)
Trimethoxyvinylsilane 2768-02-7	EC 50	> 2.500 mg/l	Bacteria	3 h		OECD Guideline 209 (Activated Sludge, Respiration Inhibition Test)

12.2. Persistence and degradability

Persistence and Biodegradability:

The product is not biodegradable.

Hazardous components CAS-No.	Result	Route of application	Degradability	Method
Hexamethyldisilazane 999-97-3		no data	15,3 %	OECD Guideline 301 D (Ready Biodegradability: Closed Bottle Test)

12.3. Bioaccumulative potential / 12.4. Mobility in soil

Mobility:

Cured adhesives are immobile.

Bioaccumulative potential:

No data available.

12.5. Results of PBT and vPvB assessment

Hazardous components CAS-No.	PBT/vPvB
Hexamethyldisilazane 999-97-3	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
Trimethoxyvinylsilane 2768-02-7	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Dispose of in accordance with local and national regulations.

Collection and delivery to recycling enterprise or other registered elimination institution.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Waste code

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

SECTION 14: Transport information**14.1. UN number**

ADR	1950
RID	1950
ADN	1950
IMDG	1950
IATA	1950

14.2. UN proper shipping name

ADR	AEROSOLS
RID	AEROSOLS
ADN	AEROSOLS
IMDG	AEROSOLS
IATA	Aerosols, non-flammable

14.3. Transport hazard class(es)

ADR	2.2
RID	2.2
ADN	2.2
IMDG	2.2
IATA	2.2

14.4. Packing group

ADR
RID
ADN
IMDG
IATA

14.5. Environmental hazards

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

14.6. Special precautions for user

ADR	not applicable
-----	----------------

	Tunnelcode: (E)
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content < 10 %
(2010/75/EC)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

- H225 Highly flammable liquid and vapor.
- H226 Flammable liquid and vapor.
- H302 Harmful if swallowed.
- H311 Toxic in contact with skin.
- H332 Harmful if inhaled.
- H412 Harmful to aquatic life with long lasting effects.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.