




**Part Number :** [10081111](#)  
**Product Description :** KK Header, Vertical, Round Pin, 11 Circuits, Tin (Sn) Plating, Pin Length 19.05mm  
**Series Number :** 3003  
**Status :** Active  
**Product Category :** PCB Headers and Receptacles  
**Engineering Number :** 3003-11A



## Documents & Resources

### Drawings

[010081111\\_sd.pdf](#)  
[30030001-PK-000.pdf](#)

### 3D Models and Design Files


[STEP AP242](#)  
[SOLIDWORKS](#)  
[Creo](#)  
[Symbol and Footprint \(Multi-Format\)](#)  
[SYM-1008-1111-001.zip](#)

### Specifications

[PS-99020-0087-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	PCB Headers and Receptacles
Series	3003
Description	KK Header, Vertical, Round Pin, 11 Circuits, Tin (Sn) Plating, Pin Length 19.05mm
Application	Board-to-Board, Power, Wire-to-Board
Component Type	PCB Header
Product Name	KK 508
UPC	800753612228

### Agency

CSA	LR19980
UL	E29179

### Electrical

Current - Maximum per Contact	7.0A
Voltage - Maximum	250V

### Physical

Breakaway	No
Circuits (Loaded)	11
Circuits (maximum)	11
Color - Resin	Natural
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-2
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	2.730/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
PC Tail Length	3.94mm
Pitch - Mating Interface	5.08mm
Pitch - Termination Interface	5.08mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	No
Temperature Range - Operating	See Product Specification
Termination Interface Style	Through Hole

## Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE
Max-Cycle	1
Max-Temp	235

---

**Mates With / Use With**

**Mates with Part(s)**

Description	Part Number
KK 5.08mm Pitch Single Row Crimp Housings	<u>3001</u>
KK 5.08mm Pitch PC Board Connectors	<u>3002</u>