


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
H	-	A	INITIAL RELEASE	29NOV2013	YC BvH
		A1	ECR-14-014684	02OCT2014	GSK BvH


NOTES:
 Tolerances cable lengths:
 0m to 0.5m +30mm
 0.5m to 1.0m +50mm
 1.0m to 3.0m +100mm
 < 3.0m +1.5%



TECHNICAL DATA	
Operating voltage	max. 250 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M12 x 1 mm (recommended torque 0.6 Nm) self-securing
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)

PUR CABLE	
No./diameter of wires	3 x 0.34 mm ²
Wire isolation	PP (br, bl, bk)
C-track properties	5 million
Jacket	PUR (UL/CSA)
Outer diameter	approx. 4.3 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	-40...+80 °C
Temperature range (mobile)	-25...+80 °C

PVC CABLE	
No./diameter of wires	3 x 0.34 mm ²
Wire isolation	PVC (br, bl, bk)
C-track properties	
Jacket	PVC (UL/CSA)
Outer diameter	approx. 4.6 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	-30...+80 °C
Temperature range (mobile)	-5...+80 °C



LENGTH "L"	MATERIAL	JACKET COLOR	TE PN	DESCRIPTION	ITEM
3 pos	PVC	Black	1-2273116-5	3x22AWG PVC 2.0m	10
			1-2273116-4	3x22AWG PVC 1.5m	9
			1-2273116-3	3x22AWG PVC 1.0m	8
			1-2273116-2	3x22AWG PVC 0.6m	7
			1-2273116-1	3x22AWG PVC 0.3m	6
3 pos	PUR	Black	2273116-5	3x22AWG PUR 2.0m	5
			2273116-4	3x22AWG PUR 1.5m	4
			2273116-3	3x22AWG PUR 1.0m	3
			2273116-2	3x22AWG PUR 0.6m	2
			2273116-1	3x22AWG PUR 0.3m	1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	YATHISH.C	29NOV2013	TE Connectivity NAME M12 STRGT PLUG TO M12 ANGLED SOCKET AA
CHK	B.VELDHOVEN	29NOV2013	
APVD	A.VAN ZANDVOORT	29NOV2013	
PRODUCT SPEC			
APPLICATION SPEC			108-19483
WEIGHT			114-32127
CUSTOMER DRAWING			SIZE: A3 CAGE CODE: 00779 DRAWING NO: C-2273116 RESTRICTED TO: -
SCALE			NTS
SHEET			1 OF 1
REV			A1

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
MATERIAL	FINISH
-	-