

SSR-480A125

✓ ACTIVE

Potter & Brumfield | Potter & Brumfield SSR

TE Internal #: 1-1393030-3

AC Input Solid State Relay, 1 Form A SPST-NO, 48 – 660 Vrms
Output, AC Output, Panel Mount, Black, Potter & Brumfield SSR

[View on TE.com >](#)



Relays & Contactors > Solid State Relays > Solid State Relays, P&B SSR Series



Input Current Type: AC
Contact Arrangement: 1 Form A SPST-NO
Output Voltage Rating: 48 – 660 Vrms
Output Switching: Zero
Output Current Type: AC

[All Solid State Relays, P&B SSR Series \(10\)](#)

Features

Configuration Features

Contact Arrangement	1 Form A SPST-NO
---------------------	------------------

Electrical Characteristics

Output Voltage Rating	48 – 660 Vrms
-----------------------	---------------

Body Features

Device Package Style	Hockey Puck
Primary Product Color	Black
Product Weight	98 g[3.45 oz]

Termination Features

Relay Connection Type	Terminals
Terminal Configuration	Screw Terminals

Mechanical Attachment

Product Mounting Feature Type	Mounting Hole
Product Mount Type	Panel Mount



Dimensions

Product Length	45 mm[1.77 in]
Product Width	43.4 mm[1.7 in]
Product Height	57.8 mm[2.27 in]

Usage Conditions

Operating Temperature Range	-30 – 80 °C[-22 – 176 °F]
-----------------------------	---------------------------

Operation/Application

Input Current Type	AC
Output Switching	Zero
Output Current Type	AC

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 2323803-1
SSR-ACC-TH-001 = Thermal pad 1 phase

Also in the Series | Potter & Brumfield SSR



Relay Accessories(1)




Solid State Relays(24)

Customers Also Bought



TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM,
CONNECTOR HOUSING



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #114017-ZZ
SEALING PLUG, SIZE 12/16, WHT



TE Part #CAT-D48-ST273
DEUTSCH Solid Contacts



TE Part #DT04-2P
REC, 2P, GRY, N



TE Part #DT06-2S
PLG, 2P, GRY, N



TE Part #CAT-D487-W416
Wedge locks: DEUTSCH DT

Documents

CAD Files
Customer View Model
[ENG_CVM_CVM_1-1393030-3_26.3d_igs.zip](#)
English
Customer View Model



[ENG_CVM_CVM_1-1393030-3_26.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1393030-3_26.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SSR_Datasheet](#)

English

SSR, SSRD and SSRT Series

English

Agency Approvals

[UL](#)

English