


FEATURES

- **Annealed Copper Conductor:** Provides superior conductivity and durability
- **Polyvinyl Chloride Jacket:** Offers protection against environmental factors
- **5 Core Design:** Suitable for complex wiring requirements
- **Temperature Range -15 °C to 70 °C:** Ensures performance in diverse conditions
- **Voltage Rating of 500 V:** Suitable for high voltage applications
- **Plain Conductor Type:** Reduces oxidation and maintains performance
- **100 m Cable Length:** Provides ample length for extensive installations

RS PRO 0.75 mm² Flexible Cable, 5 Core

RS Stock No: 606-081



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible cable is designed for reliable performance in various electrical applications. With a conductor made of annealed copper, it ensures excellent conductivity and durability. The cable is suitable for installations requiring flexibility and a robust design, making it ideal for both industrial and domestic environments.

General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	White
Product Type	Flexible Cable

Mechanical Specifications

Cable CSA	0.75 mm ²
Cable Length	100 m
Core Strands	24/0.2
Jacket Material	Polyvinyl Chloride
Number of Cores	5
Outside Diameter	9.3 mm

Operation Environment Specifications

Maximum Operating Temperature	70 °C
Minimum Operating Temperature	-15 °C

Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	---

Electrical Specifications

Voltage	500 V
---------	-------