



SITOR fuse holder 22x 127 63 A 1500 V AC/1000 V DC 2-pole

Model		
product brand name	SITOR	
product designation	SITOR fuse switch disconnecter	
design of the actuating element	swivel knob	
General technical data		
number of poles	2	
size of fuse link	22x127	
utilization category	AC20B/DC20B	
size of the fuse link	22x127 mm	
operating voltage		
• at AC rated value maximum	1 500 V	
• at DC rated value maximum	1 000 V	
Protection class		
protection class IP on the front	IP20	
Main circuit		
operational current rated value	63 A	
Suitability		
suitability for use main switch	No	
suitability for use switch disconnector	No	
suitability for use EMERGENCY OFF switch	No	
suitability for use safety switch	No	
Product function		
product function fuse monitoring	No	
Short circuit		
conditional short-circuit current (I _q) rated value	50 kA	
Connections		
connectable conductor cross-section solid		
• minimum	1 mm ²	
• maximum	50 mm ²	
type of electrical connection for main current circuit	screw-type terminals	
Mechanical Design		
height	200 mm	
depth	102 mm	
fastening method		
• floor mounting	Yes	
• rail mounting	No	
net weight	961 g	
Approvals Certificates		
General Product Approval	other	Environment



[Miscellaneous](#)

[Confirmation](#)

[Environmental Confirmations](#)

Environment

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NC2392-0MK>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NC2392-0MK>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC2392-0MK


CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





last modified:

4/12/2025 

