


Halogen Machine Luminaire




HSWT 20

connected load	24 V; AC/DC
fitted with	1 x halogen lamp QR-CB51 20 W
radiation characteristic	10 ° spot
work equipment	without
mains lead	approx. 1.5 m; with free stranded wires
luminaire body	
material	plastic
tubular sections	
material	flexible metal tube
weight (net)	approx. 0,8 kg
fastening	screw-down flange~table clamp (accessory)~wall bracket (accessory)
technology	switchable
usage	switch
lamp cover	twin glass screen
glare-free	metal louvre
balance of articulation joints	friction
system of protection	IP 65
class of protection	I
colour luminaire body	Jet black
colour of tubular sections	Jet black
article no.	112049010



E_{min}: 48 lx
 E_m: 1295 lx
 E_{max}: 12740 lx



measuring conditions: 50

