




Ø1.87~2.45		0.55~1.39mm ² (AWG# 16~20, AVS-0.5)		51128-***01 51097-***00		黄銅、錫メッキ材 TIN PLATED BRASS t=0.2	50350-9101	バラ状 LOOSE
Ø2~2.6		0.56~1.29mm ² (AVS-0.5~1.25相当) (CORRESPOND TO AVS-0.5~1.25)		51120-***0*				
Ø1.87~2.45		0.55~1.39mm ² (AWG# 16~20)		51128-***01 51097-***00				
Ø2~2.6		0.56~1.29mm ² (AVS-0.5~1.25相当) (CORRESPOND TO AVS-0.5~1.25)		51120-***0*			50350-9001	連鎖状 CHAIN
被覆外形 INS. RANGE		適用電線範囲 WIRE RANGE		適用ハウジング APPLICABLE HOUSING		材料 MATERIAL	ENG. NO.	端子形状 FORM
REVISED EC NO: J2006-0425 DRW: HVAJIMA 2005/11/07 CHK: DN. UKITA 2005/11/07 APPR: NUKITA 2005/11/11	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 10:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
		10 UNDER ±0.2		DRAWN BY DATE M. SANO '92/03/18		TITLE 2.5/3.0 WIRE TO BORAD CONN. CRIMP RECEPTACLE		
		10 OVER 30 UNDER ±0.25		CHECKED BY DATE M. SANO M. SAK '95/06/27				
		30 OVER ±0.3		APPROVED BY DATE M. ENOMOTO '95/06/27		MOLEX INCORPORATED		
		ANGULAR ±3 °		MATERIAL NO.				
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		SEE CHART SD-50350-9*01		1 OF 1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								