



Technical data

4T-33889/33822


Single row tapered roller bearings

Mounted cone, pressed steel cage


KIT CONTENT

4T-33889, 4T-33822

VISUAL (S)



4T-33889/33822
Single row tapered roller bearings



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	50,8 mm
D - External diameter	95,25 mm
B - Bearing/Inner ring width	28,575 mm
C - Outer ring width	22,225 mm
T - Total width	28,575 mm
d1 - External diameter inner ring	72,5 mm
a - Charge load application point	0 mm
rs - Min fillet radius	3,5 mm
r1s - Min fillet radius	0,8 mm
Mass	0,879 kg

PRODUCT PERFORMANCE

C - Dynamic load	119 kN
------------------	--------



PRODUCT PERFORMANCE

C0 - Static load	139 kN
Cu - Fatigue limit load	17 kN
A2 - Rating life coefficient	1
e - Coefficient	0.33
Y0 - Static axial load coefficient	1
Y2 - Upper axial load coefficient	1.82
N lim - Oil lubrication limit speed	5200 tr/min
N lim - Grease lubrication limit speed	3900 tr/min
Tmin - Min operating temperature	-40 °C
Tmax - Max operating temperature	120 °C

ABUTMENT

da max - Max shoulder diameter IR	58 mm
db min - Min IR shoulder diameter	64 mm
Da max - Max shoulder diameter OR	86 mm
Db min - Min OR shoulder diameter	90 mm
ra max - Max fillet radius	3,5 mm
r1a - Max fillet radius	0,8 mm

KIT COMPONENT

Cone designation	4T-33889
Cup designation	4T-33822

ESHOPDONOTDISPLAY

Tracepart	Oui/Yes
Reference	4T-33889/33822



ESHOPDONOTDISPLAY

Image	TRBCM_1.jpg, TRBCM_2.jpg, TRBCM_3.jpg
ULTAGE	Non/No
Rolling element material	Acier de cémentation

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$$P = X.F_r + Y.F_a$$

$F_a / F_r \leq e$		$F_a / F_r > e$	
X	Y	X	Y
1	0	0.4	Y ₂

Equivalent static radial load

$$P_0 = X_0.F_r + Y_0.F_a$$

X_0	Y_0
0.5	Y ₀

If $P_0 \leq F_r$, then use $P_0 = F_r$

The values for e, Y₂ and Y₀ are shown in the above table

