

**Productname :** CORROSION INHIBITOR  
**Ref.Nr.:** UDS000523\_3\_20191111 (EN)

**Creationdate :** 11.11.19 Version : 3.1  
**Replaces:** UDS000523\_20190703

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

**CORROSION INHIBITOR**  
Aerosol

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Anti Corrosion Products

### 1.3. Details of the supplier of the safety data sheet

**CRC Industries UK Ltd.**  
Wylds Road  
Castlefield Industrial Estate  
TA6 4DD Bridgwater Somerset  
United Kingdom  
Tel.: +44 1278 727200  
Fax.: +44 1278 425644  
E-mail : hse.uk@crcind.com

### 1.4. Emergency telephone number

(+44)(0)1278 72 7200 (office hours)

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

#### Classification according to Regulation (EC) No 1272/2008

**Physical:** Aerosols, category 1  
Extremely flammable aerosol.  
Pressurised container: May burst if heated.

Classification is based on test data.

**Health:** Eye irritation, category 2  
Causes serious eye irritation.

Classification based on calculation method.

**Environment:** Hazardous to the aquatic environment, chronic category 2  
Toxic to aquatic life with long lasting effects.

Classification based on calculation method.

### 2.2. Label elements



1 / 10

**CRC Industries UK Limited**  
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
Somerset, TA6 4DD  
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

**Productname :** CORROSION INHIBITOR  
**Ref.Nr.:** UDS000523\_3\_20191111 (EN)

**Creationdate :** 11.11.19 Version : 3.1  
**Replaces:** UDS000523\_20190703

### Labelling according to Regulation (EC) No 1272/2008

**Hazard pictogram(s):**



<b>Signal word:</b>	Danger
<b>Hazard statement(s):</b>	H222 : Extremely flammable aerosol. H229 : Pressurised container: May burst if heated. H319 : Causes serious eye irritation. H411 : Toxic to aquatic life with long lasting effects.
<b>Precautionary statement(s):</b>	P102 : Keep out of reach of children. P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 : Do not spray on an open flame or other ignition source. P251 : Do not pierce or burn, even after use. P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. P501-2 : Dispose of contents/container to an authorised waste collection point.
<b>Supplemental Hazard information:</b>	Repeated exposure may cause skin dryness or cracking. Contains: Benzene,mono-C10-13 alkyl derivs,distsulfonated May produce an allergic reaction.

### 2.3. Other hazards

No information available

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable.

### 3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
Hydrocarbons, C10-C12, Isoalkanes, less than 2% aromatics	01-2119471991-29	-	(923-037-2)	60-100	Flam. Liq. 3, Asp. Tox. 1, Aquatic Chronic 2	H226,H304,H411	Q
carbon dioxide	-	124-38-9	204-696-9	5-10	Press. Gas	H280	A,G
(2-methoxymethylethoxy)propanol	01-2119450011-60	34590-94-8	252-104-2	1-5	-	-	A
ethanol; ethyl alcohol	01-2119457610-43	64-17-5	200-578-6	1-5	Flam. Liq. 2, Eye Irrit. 2	H225,H319	B,X,W
Benzene,mono-C10-13 alkyl derivs,distsulfonated	01-2120767409-42	-	(947-582-0)	0-5	Skin Sens. 1	H317	

**Productname :** CORROSION INHIBITOR  
**Ref.Nr.:** UDS000523\_3\_20191111 (EN)

**Creationdate :** 11.11.19 Version : 3.1  
**Replaces:** UDS000523\_20190703

(Z)-N-methyl-N-(1-oxo-9-octadecenyl)glycine	01-2119488991-20	110-25-8	203-749-3	0-1	Acute Tox. 4, Skin Irrit. 2, Eye Dam. 1, Aquatic Acute 1	H332,H315,H318,H400	B
methanol	01-2119433307-44	67-56-1	200-659-6	0-1	Flam. Liq. 2, Acute Tox. 3, Acute Tox. 3, STOT SE 1	H225,H331,H311,H301,H370	A,X
1H-Imidazole-1-ethanol, 2-(8-heptadecenyl)-4,5-dihydro-	01-2119777867-13	95-38-5	202-414-9	0-1	Acute Tox. 4, Skin Corr. 1B, STOT RE 2, Aquatic Acute 1, Aquatic Chronic 1	H302,H314,H373,H400,H410	

**Explanation notes**

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

G : exempted from the obligation to register in accordance with art.2(7)of REACH Regulation No 1907/2006

Q : The CAS-no is only an indicative identifier to be used outside the EU for global inventory entries.

W : Note: substance mentioned on the list of CMR-substances of the Dutch Ministry of Social Affairs and Employment (SZW)

X : SCL (specific concentration limit)in accordance with art.10 of CLP Regulation No 1272/2008

(\* Explanation phrases : see chapter 16)

**SECTION 4: First aid measures****4.1. Description of first aid measures**

<b>Contact with eyes :</b>	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
<b>Contact with skin :</b>	Take off contaminated clothing and wash before reuse. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.
<b>Inhalation :</b>	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
<b>Ingestion :</b>	If swallowed accidentally, do not induce vomiting and seek medical advice.

**4.2. Most important symptoms and effects, both acute and delayed**

<b>Inhalation :</b>	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	May cause gastrointestinal disturbances Symptoms : sore throat, abdominal pain, nausea, vomiting
<b>Skin contact :</b>	May cause irritation. Symptoms : redness and pain
<b>Eye contact :</b>	Irritating to eyes Symptoms : redness and pain

**4.3. Indication of any immediate medical attention and special treatment needed**

<b>General Advice :</b>	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

**SECTION 5: Firefighting measures**


3 / 10

**CRC Industries UK Limited**

Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
Somerset, TA6 4DD

Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

**Productname :** CORROSION INHIBITOR  
**Ref.Nr.:** UDS000523\_3\_20191111 (EN)

**Creationdate :** 11.11.19 Version : 3.1  
**Replaces:** UDS000523\_20190703

### 5.1. Extinguishing media

foam, carbon dioxide or dry agent

### 5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C  
Forms hazardous decomposition products  
CO,CO2

### 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources  
Ensure adequate ventilation  
Wear suitable protective clothing and gloves.

### 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses  
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

### 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material  
Place in appropriate container

### 6.4. Reference to other sections

For further information see section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
Take precautionary measures against static discharges  
Equipment should be earthed  
Use explosion-proof electrical/ventilating/lighting/.../equipment.  
Use only non-sparking tools.  
Do not breathe aerosols or vapours.  
Ensure adequate ventilation  
Avoid contact with skin and eyes.



**Productname :** CORROSION INHIBITOR  
**Ref.Nr.:** UDS000523\_3\_20191111 (EN)

**Creationdate :** 11.11.19 Version : 3.1  
**Replaces:** UDS000523\_20190703

Wash thoroughly after use  
 Wear protective gloves/protective clothing/eye protection/face protection.  
 Eyewash bottles should be available

## 7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.  
 Keep out of reach of children.

## 7.3. Specific end use(s)

Anti Corrosion Products

# SECTION 8: Exposure controls/personal protection

## 8.1. Control parameters

### Exposure limits :

Hazardous ingredient	CAS-nr.	method	
<b>EU established exposure limits:</b>			
carbon dioxide	124-38-9	TWA	9000 mg/m3
		STEL	mg/m3
(2-methoxymethylethoxy)propanol	34590-94-8	TWA	50 ppm
methanol	67-56-1	TWA	200 ppm
<b>National established exposure limits, United Kingdom</b>			
carbon dioxide	124-38-9	TWA	5000 ppm
		STEL	15000 ppm
(2-methoxymethylethoxy)propanol	34590-94-8	TWA	50 ppm
ethanol; ethyl alcohol	64-17-5	TWA	1000 ppm
methanol	67-56-1	TWA	200 ppm
		STEL	250 ppm
<b>National established exposure limits, Ireland</b>			
carbon dioxide	124-38-9	TWA	5000 ppm
		STEL	15000 ppm
(2-methoxymethylethoxy)propanol	34590-94-8	TWA	50 ppm
		STEL	-
ethanol; ethyl alcohol	64-17-5	STEL	1000 ppm
methanol	67-56-1	TWA	200 ppm
		STEL	-

## 8.2. Exposure controls

**Control procedures :** Ensure adequate ventilation  
 Keep away from heat and sources of ignition  
 Take precautionary measures against static discharges

**Personal protection :** Take precautions to avoid contact with skin and eyes when handling the product.



5 / 10

**CRC Industries UK Limited**  
 Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
 Somerset, TA6 4DD  
 Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

**Productname :** CORROSION INHIBITOR  
**Ref.Nr.:** UDS000523\_3\_20191111 (EN) **Creationdate :** 11.11.19 Version : 3.1  
**Replaces:** UDS000523\_20190703

<b>inhalation :</b>	Ensure adequate ventilation Wear suitable protective gloves In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	Air purifying respirator equipped with organic gas/vapor cartridge (type A)
<b>hands and skin :</b>	When handling the product wear chemical-resistant gloves (standard EN 374). The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through.
Recommended gloves:	Nitrile
<b>eyes :</b>	Wear safety eyewear according to EN 166.
<b>Environmental protection:</b>	Avoid release to the environment. Collect spillage.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

<b>Apperance : physical state :</b>	Liquid under pressure.
<b>colour :</b>	Brown.
<b>odour :</b>	Characteristic odor.
<b>pH :</b>	Not applicable.
<b>Boiling point/range :</b>	77 °C
<b>Flash point :</b>	39 °C (Closed Cup)
<b>Explosion limits : upper limit :</b>	19 %
<b>lower limit :</b>	0.6 %
<b>Relative density :</b>	0.810 g/cm <sup>3</sup> (@ 20°C).
<b>Solubility in water :</b>	Insoluble in water
<b>Auto-ignition :</b>	> 200 °C
<b>Viscosity :</b>	Not available.

### 9.2. Other information

<b>VOC = volatile organic compounds</b>	602 g/l
---	---------

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

### 10.2. Chemical stability

Stable

### 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose



6 / 10

**CRC Industries UK Limited**  
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
Somerset, TA6 4DD  
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

**Productname :** CORROSION INHIBITOR  
**Ref.Nr.:** UDS000523\_3\_20191111 (EN)

**Creationdate :** 11.11.19 Version : 3.1  
**Replaces:** UDS000523\_20190703

#### 10.4. Conditions to avoid

Avoid overheating

#### 10.5. Incompatible materials

Strong oxidising agent

#### 10.6. Hazardous decomposition products

CO,CO2

### SECTION 11: Toxicological information

#### 11.1. Information on toxicological effects

<b>acute toxicity:</b>	based on available data the classification criteria are not met
<b>skin corrosion/irritation:</b>	based on available data the classification criteria are not met
<b>serious eye damage/irritation:</b>	Causes serious eye irritation.
<b>respiratory or skin sensitisation:</b>	based on available data the classification criteria are not met
<b>germ cell mutagenicity:</b>	based on available data the classification criteria are not met
<b>carcinogenicity:</b>	based on available data the classification criteria are not met
<b>toxicity for reproduction:</b>	based on available data the classification criteria are not met
<b>STOT-single exposure:</b>	based on available data the classification criteria are not met
<b>STOT repeated exposure:</b>	based on available data the classification criteria are not met
<b>aspiration hazard:</b>	based on available data the classification criteria are not met

#### Information on likely routes of exposure:

<b>Inhalation :</b>	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	May cause gastrointestinal disturbances
<b>Skin contact :</b>	May cause irritation.
<b>Eye contact :</b>	Irritating to eyes

#### Toxicological data :

Hazardous ingredient	CAS-nr.	method	
(2-methoxymethylethoxy)propanol	34590-94-8	LD50 oral rat	> 5000 mg/kg
		LD50 derm.rabit	> 10000 mg/kg
ethanol; ethyl alcohol	64-17-5	LD50 oral rat	> 2000 mg/kg
		LD50 derm.rabit	> 2000 mg/kg

### SECTION 12: Ecological information

**Productname :** CORROSION INHIBITOR  
**Ref.Nr.:** UDS000523\_3\_20191111 (EN)

**Creationdate :** 11.11.19 Version : 3.1  
**Replaces:** UDS000523\_20190703

### 12.1. Toxicity

Hazardous to the aquatic environment, chronic category 2  
Toxic to aquatic life with long lasting effects.

### Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
(2-methoxymethylethoxy)propanol	34590-94-8	IC50 algae	> 100 mg/l
		LC50 fish	> 10000 mg/l
		EC50 daphnia	> 100 mg/l
ethanol; ethyl alcohol	64-17-5	LC50 fish	> 100 mg/l

### 12.2. Persistence and degradability

No information available

### 12.3. Bioaccumulative potential

No information available

### 12.4. Mobility in soil

Insoluble in water

### 12.5. Results of PBT and vPvB assessment

No information available

### 12.6. Other adverse effects

No information available  
GWP (global warming potential): 0

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

**National regulations :** Disposal should be in accordance with local, state or national legislation

## SECTION 14: Transport information

### 14.1. UN number

UN-number : 1950

### 14.2. UN proper shipping name



8 / 10

**CRC Industries UK Limited**  
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
Somerset, TA6 4DD  
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com



**Productname :** CORROSION INHIBITOR  
**Ref.Nr.:** UDS000523\_3\_20191111 (EN) **Creationdate :** 11.11.19 Version : 3.1  
**Replaces:** UDS000523\_20190703

Proper shipping name: AEROSOLS (Hydrocarbons, C10-C12, Isoalkanes, less than 2% aromatics)

#### 14.3. Transport hazard class(es)

Class: 2.1  
ADR/RID - Classification code: 5F

#### 14.4. Packing group

Packing group: Not applicable.

#### 14.5. Environmental hazards

ADR/RID - Environmentally hazardous: Yes  
IMDG - Marine pollutant: Marine pollutant  
IATA/CAO - Environmentally hazardous: Yes

#### 14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)  
IMDG - Ems: F-D, S-U  
IATA/CAO - PAX: 203  
IATA/CAO - CAO: 203

#### 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.  
Regulation (EC) No 1907/2006 (REACH)  
Regulation (EC) No 1272/2008 (CLP)  
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

#### 15.2. Chemical safety assessment

No information available

### SECTION 16: Other information

\*Explanation hazard statements: - : -  
H225 : Highly flammable liquid and vapour.  
H226 : Flammable liquid and vapour.



**Productname :** CORROSION INHIBITOR  
**Ref.Nr.:** UDS000523\_3\_20191111 (EN)

**Creationdate :** 11.11.19 Version : 3.1  
**Replaces:** UDS000523\_20190703

H280 : Contains gas under pressure; may explode if heated.  
H301 : Toxic if swallowed.  
H302 : Harmful if swallowed.  
H304 : May be fatal if swallowed and enters airways.  
H311 : Toxic in contact with skin.  
H314 : Causes severe skin burns and eye damage.  
H315 : Causes skin irritation.  
H317 : May cause an allergic skin reaction.  
H318 : Causes serious eye damage.  
H319 : Causes serious eye irritation.  
H331 : Toxic if inhaled.  
H332 : Harmful if inhaled.  
H370 : Causes damage to organs .  
H373 : May cause damage to organs through prolonged or repeated exposure .  
H400 : Very toxic to aquatic life.  
H410 : Very toxic to aquatic life with long lasting effects.  
H411 : Toxic to aquatic life with long lasting effects.

acronyms and synonyms:

TWA = time weight average  
STEL = short time exposure limit  
VOC = volatile organic compounds  
PBT = persistant bioaccumulative toxic  
vPvB = very persitant very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.