



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Panel Mount Shroud**  
Primary Product Color: **Black**  
Primary Product Material: **PA 66**  
Operating Temperature (Max): **85 °C [ 185 °F ]**  
Operating Temperature Range: **-20 – 85 °C [ -4 – 185 °F ]**

Features

Product Type Features

Connector Cover Type	Panel Mount Shroud
----------------------	--------------------

Body Features

Primary Product Color	Black
Primary Product Material	PA 66

Housing Features

Compatible With Connector Shape	Rectangular
---------------------------------	-------------

Dimensions

Product Width	29.6 mm
Product Length	45.6 mm
Product Height	14 mm

Usage Conditions

Compatible With Connector Style	Plug
Operating Temperature (Max)	85 °C[185 °F]
Operating Temperature Range	-20 – 85 °C[-4 – 185 °F]

Operation/Application



Compatible With Connector Shell Size	48
--------------------------------------	----

Packaging Features

Packaging Method	Bag/Box
Packaging Quantity	10

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2295891-1  
SCREEN CLAMP; MOTORMAN SHROUD



TE Part # 2295895-1  
SIDE CLIP, PLASTIC




Also in the Series | MotorMan



Circular Connector Contact Inserts(2)



Connector Caps & Covers(2)



Connector Hardware(4)




Connector Seals & Cavity Plugs(2)



Connector Strain Relief(2)



Rectangular Connector Hoods & Bases (4)



Rectangular Contact Inserts(5)

Customers Also Bought



TE Part #2280628-6  
ANVIL, BLUNT



TE Part #45216  
DAHT AMP CLOSED END SPLICES 22-14 ASSY



TE Part #3-2176412-8  
5W XSM M/OX 5% 180R




TE Part #826925-8  
8P MOD2 STIFT LEI



TE Part #1SNG625005R0000  
EM-SGL-M16-MET-E



TE Part #2176413-2  
5W XSM M/OX 5% 75K



TE Part #3-215297-6  
36P HV100 REC CON. TE, 7.0MM



TE Part #8-2176416-6  
9W STD M/OX 5% 180K



TE Part #T41511C9L25-003  
RPC-M12L-5MS-1.5-PUR 16AWG GY



TE Part #1337772-2  
50/OHM COAX BNC STR PLUG ELB P



Documents

Product Drawings

SHROUD PLASTIC

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2295892-1\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2295892-1\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2295892-1\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English