



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Cadmium oxide (10% in Component Part) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1419106-7

27E220=SOCKET,KH,8,PL,PHEN,BLK

Customers Also Bought

TE Part #1-1437624-8

PKAP50B1/4=KNOB PLASTIC W/POIN

TE Part #8-1393117-3

KUP-14A25-120=KU

TE Part #1415526-1

PT78722

TE Part #1-745496-8

25 HDE MS PLUG,22-26,LEAD FREE

TE Part #192004-8

BAND STRIP LA1A(.006)SIL

TE Part #929963-1

STIFTKONTAKT 2,5MMD

TE Part #640251-3

03P SL156 HSG W/O RAMP NATL

TE Part #7-1393114-0

KUHP-11A51-24=KU-

TE Part #2-1393123-8

KHU-17A11N-120=KH

TE Part #6609015-3

3EF1F=F7323 S0

Documents

- CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1393122-6_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1393122-6_C.3d_igs.zip

English



Customer View Model

[ENG_CVM_CVM_1-1393122-6_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[KHA General Purpose Dry Circuit to 5A Multicontact AC or DC Relay](#)

English

Product Specifications

[Definitions General Purpose Relays](#)

English

Agency Approvals

[UL](#)

English