

PRODUCT-DETAILS

A87NP

NON-INS RNG 22-16 No10 NKLPLT



Product image
not available

General Information

Extended Product Type	A87NP
Product ID	7TAI029650R0060
EAN	0786209914491
Catalog Description	NON-INS RNG 22-16 No10 NKLPLT
Long Description	Non-Insulated Ring Terminal, Length .75 Inches, Width .31 Inches, Bolt Hole #10, Wire Range #22-#16 AWG, Copper, Nickel Plated, 1,000 Pack

Ordering

EAN	0786209914491
UPC	786209914491

Dimensions

Product Net Length	0, mm
--------------------	-------

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	3 in 76 mm
Package Level 1 Height	3.5 in 89 mm

Package Level 1 Depth / Length	3 in 76 mm
Package Level 2 Units	5000 piece
Package Level 2 Width	3.62 in 92 mm
Package Level 2 Height	16.12 in 409 mm
Package Level 2 Depth / Length	6.5 in 165 mm

Additional Information

Brand / Label	Sta-Kon
Effective Date	20150528
Material	Copper
Number of Batteries	0
Product Name	ELECTRICAL TERMINAL,<1000V
Product Type	Non-Insulated Ring Terminal
Special Functions	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.
Wire Size	22-16 AWG

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	A87NP
Instructions and Manuals	A87NP

Classifications

ETIM 6	EC001052 - Solderless copper terminals for copper conductors
ETIM 7	EC001052 - Solderless copper terminals for copper conductors
UNSPSC	39121432
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4603 >> Electrical terminals

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors



Product image
not available