



Connectors > Connector Accessories > Connector Hardware > Quick Lock Pins for D-Sub with Threaded Inserts



Connector Hardware Accessory Type: **Quick Lock Pins**  
Operating Temperature (Max): **90 °C [ 194 °F ]**  
Operating Temperature Range: **-40 – 90 °C [ -40 – 194 °F ]**  
Hardware Accessory Function: **Latching, Locking & Retention**

[All Quick Lock Pins for D-Sub with Threaded Inserts \(10\)](#)

Features

Product Type Features

|                                   |                               |
|-----------------------------------|-------------------------------|
| Connector Hardware Accessory Type | Quick Lock Pins               |
| Hardware Accessory Function       | Latching, Locking & Retention |

Mechanical Attachment

|             |      |
|-------------|------|
| Thread Size | None |
|-------------|------|

Usage Conditions

|                             |                           |
|-----------------------------|---------------------------|
| Operating Temperature (Max) | 90 °C[194 °F]             |
| Operating Temperature Range | -40 – 90 °C[-40 – 194 °F] |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|                                               |                                             |
|-----------------------------------------------|---------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant with Exemptions                   |
| EU ELV Directive 2000/53/EC                   | Not Yet Reviewed                            |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold        |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247) |



Candidate List Declared Against: JAN 2024  
(240)  
SVHC > Threshold:  
Pb (3.5% in Component Part)

**Article Safe Usage Statements:**  
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

|                           |                                                                                     |
|---------------------------|-------------------------------------------------------------------------------------|
| Halogen Content           | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not reviewed for solder process capability                                          |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1-2308327-1  
FULL METAL HOODS SIZE 3 (1)

TE Part # 1-2308321-1  
FULL METAL HOODS SIZE 2, (1)

TE Part # 1-2308330-1  
FULL METAL HOODS SIZE 4 (1)


TE Part # 1-2308319-1  
FULL METAL HOODS SIZE 1 (1)

TE Part # 1-2308338-1  
QL-FULL METAL HOODS SIZE 5 (1  
CABLE CLP)

Also in the Series | Rail D-Sub Backshells



Connector Contacts(5)




Connector Hardware(19)



Connector Strain Relief(67)



Crimp D-Sub Connectors(10)




D-Sub Backshells & Clamps(55)

Customers Also Bought



TE Part #1-2308290-1  
QL-SET FOR VARIAN C REAR WALL MOUNTG



TE Part #592629-7  
TERM JCT,F/B SZ 21,34 BUSS



TE Part #EG1834-000  
SHF260-0813-00-9



TE Part #2560-201-2031L  
CONT PIN



TE Part #1-2308273-1  
QL-SET VAR A W/STP MO FOR COMBLOCK M3THD



TE Part #48131  
HYP8 SOLIS 1/0-4/0AWG INDENTER



TE Part #322365  
DG 22-16COM22-18MIL HR R 8



TE Part #323177  
STRATO-THERM, HR 2 3/8 NIPL



TE Part #48133  
HYP8 SOLIS 2/0AWG NEST



TE Part #322364  
DG 22-16COM22-18MIL HR R 6

Documents



Product Drawings

QL SET FOR VARIANT B 10

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2-2308265-0\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-2308265-0\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-2308265-0\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Rail D-Sub Backshells Flyer

English