



CHAMP | CHAMP Docking Connectors


TE Internal #: 554084-1

TE Internal Description: PLUG ASSY,36 POS,BAIL LOCK,LPF

IDC D-Sub: Plug Assembly, Signal, Cable to Cable, 2.16 mm

[View on TE.com >](#)

Connectors > D-Shaped Connectors > IDC D-Sub: Plug Assembly, Signal, Cable to Cable, 2.16 mm



Number of Positions: **36**

Connector & Housing Type: **Plug**

Connector System: **Cable-to-Cable**

Connector Mounting Type: **Cable Mount (Free-Hanging)**

Centerline (Pitch): **2.16 mm [.085 in]**

[All IDC D-Sub: Plug Assembly, Signal, Cable to Cable, 2.16 mm \(15\)](#)

Features

Product Type Features

Connector & Housing Type	Plug
Connector System	Cable-to-Cable
Connector Product Type	Connector Assembly
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	36
Number of Rows	2
Compatible With Wire & Cable Type	Ribbon Cable

Body Features

Ribbon Cable Centerline Spacing	1.27 mm[.05 in]
Connector Profile	Low
Cover Material	Thermoplastic

Contact Features

	30 μin
Contact Underplating Material	Palladium Nickel
Contact Mating Area Plating Material	Gold Flash
Contact Base Material	Phosphor Bronze

Wire Contact Termination Area Plating Material	Gold Flash
Contact Current Rating (Max)	1 A
Contact Options	Installed

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Mating Retention	With
Mating Retention Type	Screwlocks
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Thermoplastic
Centerline (Pitch)	2.16 mm[.085 in]

Dimensions

Solid Wire Size	30 – 26 AWG
Stranded Wire Size	.08 mm ²
Wire Size	30 – 26 AWG

Usage Conditions

Operating Temperature Range	-40 – 75 °C[-40 – 167 °F]
-----------------------------	---------------------------

Operation/Application

Shielded	No
Circuit Application	Signal

Packaging Features

Packaging Method	Box & Tray, Package
Packaging Quantity	100

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)

Candidate List Declared Against: JAN 2025
(247)

SVHC > Threshold:

Triphenyl phosphate (TPP) (1% in 4993802)

Article Safe Usage Statements:

Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not applicable for solder process capability




Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | CHAMP Docking Connectors





IDC D-Sub Connectors(41)



Panel Mount D-Sub Connectors(5)

Customers Also Bought



TE Part #GA10K3MBD1
MBD PROBE, 10K @25C, 0.2 FROM 0 TO 70



TE Part #ANT-916-CW-QW
Antenna 1/4 Wave Whip 916MHz




TE Part #803284-SF
FN9244-15-06




TE Part #8-188275-2
MICRO-MATCH SMD FTE



TE Part #193842-1
SKT ASSY., 2MM, 12-14 AWG



TE Part #1-640511-0
09P MR II CAP HSG V0



TE Part #3-641191-3
03P MTA100 CONN ASSY WHT LF



TE Part #2-747580-3
SHLDING FERRULE,PLTD TIN,BULK



TE Part #5555165-2
M/J, LPF, R/A, 6P/4C, TIN, BULK PKG



TE Part #6609007-3
20EEJ1=F7892A S0

Documents

Product Drawings

[PLUG ASSY,36 POS,BAIL LOCK,LPF](#)

English

CAD Files

[3D PDF](#)

English

Customer View Model

[ENG_CVM_554084-1_F.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_554084-1_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_554084-1_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

[CHAMP Latch Low Profile Connectors For Ribbon Cable](#)

English

Agency Approvals

[CSA Certificate](#)

English