



Measuring wrench, IZO-D

The IZO-D electronic tool combines accuracy and ease of operating of modern electronic torque tools with a feelable signal when the set torque range is reached. This provides a modern and precise alternative to conventional mechanical torque tools. Feedback by : FEELBACK. The correct torque value is sensed by your hand - you can rely on what you feel!

Tool body made from quality stainless steel with break-proof display cover. Tool handle from glass filled nylon incorporating a Santoprene grip.

Ranges programmable in Nm, Lbf.ft, Lbf.in. 2 scroll keys, for fast and easy programming, which are secured against accidental altering. Programmable torque value with tolerance. Accuracy 2%

Quick battery changes. Power safe feature. Dust and splash water protection. Low battery warning. Auto zero check on power up. Data and set value retention during battery exchange

Operating temperature range : 5°C - 42°C

Storage temperature range : -10°C - 50°C

Supplied with reversible ratchet head and three AA batteries.



Model	EAN	Quantity	Size	Head Size	Range 1	Range 2	Range 3	Weight	Length	Capacity
IZO-D-30	1846824	1	9x12	1/4"	3-30	2.21-22.13	26.6-265.5	6852-1	405	930
IZO-D-135	1845827	1	9x12	3/8"	7-135	5.16-99.57	62-1195	7452-1	450	1000
IZO-D-200	1846831	1	14x18	1/2"	20-200	14.75-147.50	177-1770	7852-1	535	1345
IZO-D-340	1846848	1	14x18	1/2"	34-340	25.07-250.80	301-3009	7852-1	650	1525