

CONDUIT SPECIFICATION

PART NUMBER.....PSBF07

CORE OUTSIDE DIAMETER.....38.1±0.12mm

CORE INSIDE DIAMETER.....31.35mm

COVERING MATERIAL.....RPVC01BL

WEIGHT.....980±100g/m

COLOUR.....BLACK

OUTSIDE DIAMETER.....40.35±0.12mm

MIN BEND RADIUS.....56mm

MARKING.....HOT FOIL ONCE PER METRE

.....KOPEX PLIABLE LS1 LOW ACID PVC 40mm

.....MADE IN UK \*\*\*

EXPLANATION OF \*\*\* NOTATION :-

POSITION 1 – EXTRUDER TYPE


1. BONE CRAVEN 1
2. BONE CRAVEN 2
3. MATTHEWS
4. SMALL MATTHEWS
5. FRANCIS SHAW

POSITION 2 – MONTH

- C. JANUARY
- D. FEBRUARY
- F. MARCH
- H. APRIL
- K. MAY
- M. JUNE
- P. JULY
- S. AUGUST
- T. SEPTEMBER
- V. OCTOBER
- X. NOVEMBER
- Z. DECEMBER

POSITION 3 – YEAR e.g. 2003 IS DENOTED AS 3 ONLY

KOPEX REFERENCE: 010031B-07

	MATERIAL	NO	MODIFICATIONS	DATE	INTLS
	FINISH				
	GENERAL TOLERANCE				
	UNSPECIFIED RADII				
TITLE PSBF07	ALL DIMENSIONS IN MM	1	MATERIAL CHANGED FROM 05 TO 01 (CN 05/015)	22/4/05	KJ
	DO NOT SCALE FROM DRAWING				
	DRAWN BY R.WINCOTT 13/6/03				
	APPROVED BY				
DRAWING NO. 4014	ISSUE 2				