



 PRODUCT-DETAILS

OT160EVS03K

OT160EVS03K SWITCH-DISCONNECTOR



General Information

Extended Product Type	OT160EVS03K
Product ID	1SCA120570R1001
EAN	6417019520391
Catalog Description	OT160EVS03K SWITCH-DISCONNECTOR
Long Description	3-pole, side operated, base mounted switch-diconnector with black direct mount handle, terminal bolt kit included

ABB EcoSolutions

End Of Life Disassembling Instructions	1SCC301117M0201
Environmental Information	1SCC301265D0201
Environmental Product Declaration - EPD	1SCC301282D0201

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC011021D0201
RoHS Declaration	1SCC011020D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC011025D0201

Popular Downloads

Data Sheet, Technical Information	1SCC301020C0201
Instructions and Manuals	1SCC301068M0204
Mechanical Drawings	1SCC301652F0001 1SCC301651F0001 OT200ES03K.igs
Environmental Product Declaration - EPD	1SCC301282D0201

Environmental

Degree of Protection	Front IP00
Environmental Information	1SCC301265D0201
Pollution Degree	3

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85365080
Country or Territory of Origin	Finland

Dimensions

Product Net Width	198.5 mm
Product Net Height	150 mm
Product Net Depth / Length	82 mm
Product Net Weight	1.6 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	170 mm 6.7 in
Package Level 1 Depth / Length	250 mm 9.8 in
Package Level 1 Height	155 mm 6.1 in
Package Level 1 Gross	1.8 kg

Weight	3.9 lb
Package Level 1 EAN	6417019520391

Technical

Conventional Free-air Thermal Current (I_{th})	$\Theta = 40\text{ °C}$ 200 A
Conventional Thermal Current (I_{the})	Fully Enclosed 160 A
Degree of Protection	Front IP00
Distance Between Phases	Standard
Handle Color	Black
Handle Type	Direct mounted pistol type handle
Mechanical Durability	20000
Mounting Type	Base mounting
Number of Poles	3P
Operating Mode	Side
Pollution Degree	3
Position of Line Terminals	Top In - Bottom Out Bottom In - Top Out
Power Loss	at Rated Operating Conditions per Pole 3.2 W
Rated Conditional Short-Circuit Current (I_{nc})	(315 A fuse, 500 V) 100 kA (355 A fuse, 690 V) 80 kA (250 A fuse, 690 V) 100 kA
Rated Impulse Withstand Voltage (U_{imp})	12 kV
Rated Insulation Voltage (U_i)	acc. to IEC/EN 60664-1 1000 V
Rated Operational Current AC-21A (I_e)	(380 ... 415 V) 200 A (500 V) 200 A (690 V) 200 A
Rated Operational Current AC-22A (I_e)	(380 ... 415 V) 200 A (500 V) 200 A (690 V) 160 A
Rated Operational Current AC-23A (I_e)	(380 ... 415 V) 160 A (500 V) 160 A (690 V) 160 A
Rated Operational Power AC-23A (P_e)	(220 ... 240 V) 48 kW (400 ... 415 V) 88 kW (500 V) 112 kW (690 V) 144 kW
Rated Operational Voltage	Main Circuit 1000 V
Rated Short-Circuit Making Capacity (I_{cm})	(690 V) 30 kA
Rated Short-time Withstand Current Low Voltage (I_{cw})	for 1 s 8 kA
Special Functions	No
Standards	IEC 60947-3
Switches Operating Mechanism	Mechanism at the End of the Switch 03 (Left Side)
Terminal Type	Lug terminals
Tightening Torque	acc. IEC 60947-1 15 ... 22 N·m

Technical UL/CSA

Tightening Torque

acc. IEC 60947-1 15 ... 22 N·m

Certificates and Declarations

A2L Certificate – IEC	1SCC301337D0201
ATEX Certificate	No certification needed
Declaration of Conformity - CE	1SCC301131D2705
DNV GL Certificate	1SCC301174D0204
UL Certificate	No certification needed
VDE Certificate	No certification needed

External Classifications and Standards

Object Classification Code	Q
ETIM 9	EC000216 - Switch disconnecter (low voltage)
ETIM 10	EC000216 - Switch disconnecter (AC)
UNSPSC	39122221
eClass	V11.1 : 27371403
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
E-Number (Finland)	3601474

Categories

Low Voltage Products and Systems → Switches → Switch Disconnectors

