


Through Hole - MSHH3 MSHH3-32DA

Datasheet

General series information

- Maximum gripping force 490 N at 0.5 MPa
- Double acting
- Repeatability: ± 0.01 mm
- Max. operating frequency: 120 c.p.m.




Gripper, internal grip, double-acting with permanent magnet on piston

Standard specifications

Bore Size	32mm
Port Thread	Bore 16-63: M Thread; Bore 80: Rc
Center Pusher	A (Cylinder Type)
Auto Switch	No Switch
Lead Wire or Prewired Connector	0.5m (Or None in the Case of No Switch)
Suffix for Auto Switch	2 pcs (Or None in the Case of No Switch)
Special Specifications	None
Maximum operating pressure	0.6 MPa
Minimum operating pressure	0.1 MPa
Maximum ambient temperature	60 °C
Minimum ambient temperature	-10 °C
Repeatability	± 0.01 mm
Lubrication	Non-lube
Effective holding force per finger, external (0.5 MPa)	62 N
Effective holding force per finger, internal (0.5 MPa)	77 N
Maximum operating frequency	60 c.p.m.
Fluid	Air
Action	Double Acting
Stroke per gripper jaw	8 mm

Pusher maximum operating frequency	60 c.p.m.
Pusher cylinder bore size	12 mm
Pusher stroke	5 mm
Pusher thrust N at pressure of 0.5 MPa	45 N
Weight	0.530 Kg

Dimensions



Additional information

Catalogue

[MHS_EU.pdf](#)