

Power Scraper LXT®

DHK180

18V • SDS-PLUS • 3.1 J

Chiseling and tapping conveniently with a cordless machine

18V power scraper with AVT vibration damping for chiseling and tapping. The machine uses SDS-PLUS bits. The machine produces a force of 3,1 J. The chisel can be set in 12 different positions and the stroke is adjustable between 0 and 3200 min⁻¹.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
Impact Energy	3,1 J
Impacts per Minute (IPM)	0 - 3200 min ⁻¹
Adapted for SDS-PLUS bits	✓
Tool weight with battery	3,3 – 3,6 kg
Vibration Level, Chiselling	5,7 m/s ²
Vibration Uncertainty (K Factor), Chiselling	1,5 m/s ²
Sound Power Level (L _{WA})	93 dB(A)
Sound Pressure Level (L _{pA})	85 dB(A)
Noise Uncertainty (K Factor)	2,3 dB(A)
Product Dimensions (L x W x H):	368 x 99 x 211 mm

User benefits

- 12 bit angle settings allow the bit to be set at different positions for operating convenience
- AVT (Anti-Vibration Technology) ensures extra-low vibration performance
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Variable speed control dial enables user to match the speed to the application for greater versatility
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Related products

Optional AC

198993-4

Grease vessel for bit 100 ml



821552-6

Makpac case (4)



Other

User manual

Parts drawing