

VDE 4508-05

VDE Torque wrench

5-50 Nm

Code	ETIM
3079066	EC002132
EAN	UNSPSC
4002805937280	27-11-17-15
Country of origin	eCl@ss
Germany	21-04-01-01
Customs tariff number	
82041100	



Article description

- Controlled screw tightening in the most widely used range
- Release system triggers a tactile and audible signal
- Scale with Nm division
- Classified according to DIN EN ISO 6789-2:2017 Type II Class A, incl. traceable test certificate, calibrated to a maximum permissible deviation of +/- 3 % and thus more precise than the +/- 4 % required by the standard
- Recalibration without destroying the insulation
- Fine toothed ratchet with square drive as per DIN 3120, ISO 1174
- Safety button to protect against accidental release of the insert
- VDE insulation up to 1000 V, acc. to EN 60900/IEC 60900

Article information

Contents (Qty of pieces)	1	Torque range (min./max.) [lbf·ft]	-
Net weight [kg]	0,825 kg	Trigger mechanism	Short path triggering
Total length [mm]	369 mm	Precision +/-	+/- 4 %
Total width [mm]	50 mm	Direction of tightening	Right
Total height [mm]	80 mm	Fixed setting	no
Drive connector square (male)	1/2"	Test certificate	DIN EN ISO 6789-2:2017
Drive connector square (male)	12,5 mm	Graduation	2,5
Return angle	5 °	Head height 1 [mm]	62 mm
Number of teeth	72	Width of head 1 [mm]	50,0 mm
Drive type/drive	Reversible ratchet	Calibration length	279 mm
Torque (min.) [N·m]	10 Nm	vernier Nm	0,25 Nm
Torque (max.) [N·m]	50 Nm	Distance housing - square drive	24 mm
Torque range (min./max.) [N·m]	10 Nm - 50 Nm	Storage/Content	Plastic box