



### Main

Range of product	IID
Device short name	IID
Poles description	4P
Neutral position	Left
Network type	AC

### Complementary

Device location in system	Outgoer
[In] rated current	40 A
Network frequency	50/60 Hz
[Ue] rated operational voltage	400 V EN 61008-1 AC 50/60 Hz 400/415 V IEC 61008-1 AC 50/60 Hz
Residual current tripping technology	Voltage independent
Earth-leakage sensitivity	300 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Class AC
Rated breaking and making capacity	1500 A I <sub>dm</sub> 1500 A I <sub>m</sub>
Rated conditional short-circuit current	10 kA
Contact position indicator	Yes
Control type	Toggle
Local signalling	Trip indicator
Mounting mode	Removable comb busbar installed
Mounting support	DIN rail
9 mm pitches	8
Width	72 mm
Connections - terminals	Tunnel terminal with flap

### Environment

Standards	EN 61008-1 IEC 61008-1
RoHS EUR status	Compliant
RoHS EUR conformity date	1001