

Finishing Sander LXT®

DBO382

18V, 93 x 185 mm

Model DBO382 is a cordless finishing sander powered by 18V LXT® Li-Ion battery

Hook & Loop Clamp, Electric speed control - 3 speeds H/M/L, Constant speed control



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Brushless Motor	✓
Orbits per Minute	4000 - 12000 min ⁻¹
Sanding Orbit Diameter	2,0 mm
Sound Pressure Level (L _{pA})	72 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,9 - 2,2 kg
Product Dimensions (L x W x H):	336 x 92 x 169 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Strokes per Minute (SPM)	8000 / 16000 / 24000 min ⁻¹
Vibrations per minute	4000 / 8000 / 12000 min ⁻¹
Sanding Pad Dimensions	93 x 185 mm

User benefits

- Brushless maintenance-free and long-life motor
- Electronic speed control

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing