

Features

- Excellent electrical connection
- Reduces short circuits
- Colour coded insulation for easy ferrule size identification
- Nylon insulated for reduced leakage, creepage and gas intrusion
- Tin plated copper tube for excellent conductivity
- UL Recognized

RS PRO Bootlace Ferrules

RS Stock No.: 311-7886



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS PRO a range of high-quality French/Din colour coded bootlace ferrules (also known as cord end terminals) for providing a clean end termination to multi-stranded wires. These reliable wire ferrules ensure that you have a positive connection when connecting wires to terminal blocks and captive terminals

Suitable Crimping Tools

For ferrules with a wire size range of 0.5 to 6 mm² use crimping tool stock number 683-1605

For ferrules with a wire size range of 10 to 25 mm² use crimping tool stock number 683-1614

For ferrules with a wire size range of 0.5 to 16 mm² use crimping pliers stock number 464-482

For ferrules with a wire size range of 35 or 50 mm² use crimping tool stock number 683-1617

General Specifications

Number of Entries	1
Insulation	Insulated
Insulation Material	Nylon
Colour	Blue
Contact Material	Copper
Contact Plating	Tin
Terminal Material	Copper tube
Surface Treatment	Tin plate
Insulation colour	Blue
Ferrule Type	French/Din
Pack Quantity	100
Application	Bootlace ferrules are used on multi-stranded wires that are being inserted into screw terminals and terminal blocks. Applications include consumer units, circuit breakers, electrical control panels and any equipment where there is a requirement for a multi-stranded wire connection

Electrical Specifications

Current Rating	230A
Voltage Rating	600V

Mechanical Specifications

Minimum Wire Size (mm ²)	
Maximum Wire Size (mm ²)	50mm ²
Minimum Wire Size (AWG)	
Maximum Wire Size (AWG)	1/0AWG
Pin Outside Diameter	10.9mm
Pin Inside Diameter	10.3mm
Pin Length	25mm
Overall Length	41mm
Weight	Around 3.45g per piece

Operation Environment Specifications

Maximum Temperature	105°C
---------------------	-------

Classification

eCl@ss Version	
UNSPSC Version	

Approvals

Compliance/Certifications	CE(RoHS)/ REACH / UR/ cUR/ UL94-V2
Declarations	

