



Technical data

4T-34306/34478


Single row tapered roller bearings

Tapered roller bearing, pressed steel cage


KIT CONTENT

4T-34306, 4T-34478

VISUAL (S)



4T-34306/34478
Single row tapered roller bearings



PRODUCT DEFINITION	
Brand	NTN
d - Internal diameter	77,788 mm
D - External diameter	121,442 mm
B - Bearing/Inner ring width	23,012 mm
C - Outer ring width	17,462 mm
T - Total width	24,608 mm
d1 - External diameter inner ring	98,5 mm
a - Charge load application point	25,808 mm
Mass	0,94 kg

PRODUCT PERFORMANCE	
C - Dynamic load	101 kN
C0 - Static load	127 kN
Cu - Fatigue limit load	15,5 kN

PRODUCT PERFORMANCE

A2 - Rating life coefficient	1
e - Coefficient	0.45
Y0 - Static axial load coefficient	0.73
Y2 - Upper axial load coefficient	1.33
N lim - Oil lubrication limit speed	3800 tr/min
N lim - Grease lubrication limit speed	2900 tr/min
Tmin - Min operating temperature	-40 °C
Tmax - Max operating temperature	120 °C

ABUTMENT

da max - Max shoulder diameter IR	84 mm
db min - Min IR shoulder diameter	90 mm
Da max - Max shoulder diameter OR	110 mm
Db min - Min OR shoulder diameter	116 mm
ra max - Max fillet radius	3,5 mm
r1a - Max fillet radius	2 mm

KIT COMPONENT

Cone designation	4T-34306
Cup designation	4T-34478

ESHOPDONOTDISPLAY

Tracepart	Oui/Yes
Reference	4T-34306/34478
Image	TRB_1.jpg, TRB_2.jpg, TRB_3.jpg
ULTAGE	Non/No



ESHOPDONOTDISPLAY

Rolling element material	Acier de cémentation
--------------------------	----------------------

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$P = X.F_r + Y.F_a$

$F_a / F_r \leq e$		$F_a / F_r > e$	
X	Y	X	Y
1	0	0.4	Y2

Equivalent static radial load

$P_o = X_o.F_r + Y_o.F_a$

X_o	Y_o
0.5	Y0

If $P_o \leq F_r$, then use $P_o = F_r$

The values for e, Y2 and Y0 are shown in the above table

