

Specifications

Eaton 200FEE

Eaton Bussmann series high speed British standard fuse, Double barrel, 200A, 690 VAC/500 VDC (IEC), 700 VAC/500 VDC (UL), Class aR, Breaking capacity 200 kA RMS Sym., 50 kA DC at 500 VDC

General specifications

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	200FEE
EAN	5027590466356
UPC	051712832182
PRODUCT LENGTH/DEPTH	100 mm
PRODUCT HEIGHT	22 mm
PRODUCT WIDTH	187 mm
PRODUCT WEIGHT	89.6 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized Designed and tested to BS88 part 4 IEC 60269-4

Electrical data

AMPERAGE RATING	200 A
VOLTAGE RATING	690 V (IEC), 700 V (UL)
RATED VOLTAGE AC	690 V
RATED VOLTAGE DC	500 V
INTERRUPT RATING	200 kA RMS Sym, 50 kA at 500 Vdc
CLASS	Class aR
PRE ARC (I2T)	1900
CLEARING (I2T)	7100 at 415 V, 11400 at 660 V
WATT LOSSES	52 W

Compatible Trip indicator/Microswitch

SUITABLE FOR	EC-600 Trip indicator kit (indicator + clips) TI700 Fuse indicator MAI Microswitch/adaptor MBI Microswitch/adaptor
---------------------	---

Product specifications

APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE INDICATOR	None

Resources

BROCHURES	eaton-bussmann-series-bs88-high-speed-fuses-product-aid-pa135003en-us.pdf
CATALOGS	eaton-bussmann-series-iec-high-speed-fuses-catalogue-ca135001en-en-gb.pdf
DECLARATIONS OF CONFORMITY	eaton-high-speed-british-standard-fuse-declaration-of-conformity-uk250922en.pdf eaton-high-speed-british-standard-fuse-declaration-of-conformity-eu250044en.pdf
MCAD MODEL	eaton-hs-bs88-body-fuses-mcad-3d-models-80-56-160a-200a-fee-eet.stp
TECHNICAL DATA SHEETS	720024 CT, ET, FE, EET, FEE, FM, FMM, MT, MMT fuses

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

