

BARREL EQUIPMENT



350 KG

Roulfût® pallet-removing hand trolleys

These hand trolleys enable effortless handling of drums. Models fitted with a winch are designed to place a drum onto a pallet or retrieve it from one.

- They are suitable for intensive drum handling.
- The ingenuity of the system lies in the height-adjustable self-clamping grip, which can accommodate drums of various diameters. This technique of gripping the drum from above eliminates the effort involved in sliding the drum onto a skid.
- Support leg fitted with a drum lowering shock absorber.
- Compact design.
- Single clamp for flanged drums.
- Double clamp: one for flanged drums and one for drums with a full-width opening.

Models with a lifting winch:


- Enable effortless palletising or depalletising of a drum whilst keeping the hand truck on the ground, without the need to raise or lower the hand truck onto or off the pallet. The operator is thus spared the effort of supporting the weight of the drum whilst raising or lowering it onto or off the pallet. Maximum drum lifting height on a pallet: 1080 mm.



845 008 012 – Single claw



845 008 014 – Double claw



Reference	Specifications	Barrel types	Drums	Wheel diameter (mm)	Min/max drum grip	Max. external dimensions (LxDxH)	Weight (kg)
845 008 012	Single clamp	Metal and plastic with rim	120, 220 L	300 CC + 100 CC	700 / 1080 mm	615 x 555 x 1585	23
845 008 014	Double clamp	Metal and plastic with flange and full opening					

CC: rubber

Product zoom



Single claw



Double claw



Kickstand with shock absorber