

Datasheet

RS Pro RS Series Axial Through Hole Fixed Resistor 15k Ω ±5% 1W -500 \rightarrow +350ppm/°C

RS Stock No. 739-7143



Product Details

RS Pro axial carbon resistor with $\pm 5\%$ tolerance, provides 15 k Ω resistance and is power rated at 1 W. The temperature coefficient of resistance is in the range -500 to +350 ppm/°C. Carbon film axial leaded resistor offers excellent long-term stability. It features standard solder-plated copper leads. Applications include automotive, telecommunication and medical equipment. A comprehensive range of high stability carbon film resistors are qualified and tested to the requirements of IEC 115 and IEC 115-2. The ruggedized welded cap and lead method of manufacture provides a considerable strength and resistance to damage. The coating materials and the colour bands are epoxy resin and are highly resistant to solvents, abrasion and chipping. Improvements in materials and processing have allowed the rated power to be improved. Excellent stability against changes in load conditions or moisture levels, with a low noise level and high reliability make these carbon film resistors suitable for a wide range of applications. Rated at 70°C in free air mounted horizontally.

Features and Benefits

- Available in resistances from 1 Ω to 9.1 m Ω
- Resistor body: 2.3 mm diameter, 6.3 mm length
- · Long-term stability
- Solder plated copper leads





Specifications:

Specifications.	
Case Style	Ceramic
Diameter	3.2 mm
Dimensions	3.2 (dia.) x 9 mm
Lead Diameter	0.65 mm
Length	9 mm
Maximum Operating Temperature	+155°C
Maximum Temperature Coefficient	+350 ppm/°C
Minimum Operating Temperature	-55°C
Minimum Temperature Coefficient	-500 ppm/°C
Power Rating	1 W
Resistance	15 kΩ
Technology	Carbon Film
Temperature Coefficient	-500 to +350 ppm/°C
Termination Style	Axial
Tolerance	±5%
Lead Length	26 mm
Maximum Operating Voltage	400 V
Maximum Overload Voltage	800 V



Carbon Film Leaded Resistor - RS Series



1	Ceramic Rod	4	Non-flame Paint With Sol Vent-proof
2	Tinned Iron Caps	(5)	Colour Code
3	Carbon Film	6	Lead Wire

■Dimensions

Unit: mm

Туре	L	D	Н	d	Weight (g) (1000pcs)
Carbon 0.125W	3.3+0.4/-0.2	1.8±0.3	29.3±2.0	0.452.3±0.03	92
Carbon 0.25W	6.3±0.5	2.3±0.3	28±2.0	0.55±0.03	155
Carbon 0.5W (H)	6.3±0.5	2.3±0.3	28±2.0	0.55±0.03	155
Carbon 1W (H)	9.0±0.5	3.2±0.5	26±2.0	0.65±0.03	352
Carbon 2W (H)	11.5±1.0	4.5±0.5	35±2.0	0.78±0.03	775

■Part Numbering





■Derating Curve



■Hop-Spot Temperature



■Environmental Characteristics

ltem	Requirement	Test Method
Short Time Overload	±(0.75%+0.05Ω)	JIS-C-5201-1 5.5 RCWV*2.5 or Max. overload voltage for 5 seconds
Insulation Resistance	>1000ΜΩ	JIS-C-5201-1 5.6 Apply 100V _{DC} for 1 minute
Endurance	±(3%+0.05Ω)	JIS-C-5201-1 7.10 70±2°C, Max. working voltage for 1000 hrs with 1.5 hrs "ON" and 0.5 hrs "OFF"
Damp Heat with Load	100ΚΩ±3% 100ΚΩ±5%	JIS-C-5201-1 7.9 40±2°C, 90~95% R.H. Max. working voltage for 1000 hrs with 1.5 hrs "ON" and 0.5 hrs "OFF"
Solderability	90% min. Coverage	JIS-C-5201-1 6.5 245±5°C for 3 seconds
Dielectric Withstanding Voltage	Ву Туре	JIS-C-5201-1 5.7 Apply Max. Overload Voltage for 1 minute
Temperature Coefficient	< 100KΩ +350ppm~-500ppm 100KΩ~1MΩ -0ppm~-700ppm > 1 MΩ -0ppm~-1500ppm	Resistance value at room temperature and room Temperature+100°C
Pulse Overload	±(1%+0.05Ω)	JIS-C-5201-1 5.8 4 times RCWV for 10000 cycles with 1 second "ON" and 25 seconds "OFF"
Resistance To Solvent	No deterioration of coatings and markings	JIS-C-5201-1 6.9 Trichroethane for 1 min. with ultrasonic
Terminal Strength	Tensile: 2.5 kg	Direct Load for 10 seconds In the direction off the terminal leads

- Rated Continuous Working Voltage(RCWV) = √P*R
- Storage Temperature: 25±3°C; Humidity < 80%RH



■Electrical Specifications

	Power Rating at 70°C	Operating Temp. Range	Max. Working	Max. Overload	Dielectric Withstanding	Resistance Range
Type	at 70 C	Tellip. Kalige	Voltage	Voltage	Voltage	±5%
Carbon	0.125W		150V	300V	300V	0.1Ω - 22ΜΩ
Carbon	0.25W		250V	500V	500V	1Ω - 10ΜΩ
Carbon(H)	0.5W	-55 ~ +155°C	300V	500V	500V	0.1Ω - 22ΜΩ
Carbon(H)	1W		400V	800V	800V	1Ω - 10ΜΩ
Carbon(H)	2W		500V	1000V	1000V	0.1Ω - 10ΜΩ

■Taping/Packing Specifications

Packing Methods (Ammo)



Unit: mm

Packaging	Packing Methods								
Туре	Α	B1-B2	s						
Carbon 0.125W	52+1/-0	1.2	5						
Carbon 0.25W	52+1/-0	1.2	5						
Carbon 0.5W (H)	52+1/-0	1.2	5						
Carbon 1W (H)	52+1/-0	1.5	5						
Carbon 2W (H)	52+1/-0	1.5	10						

Ammo Packing



Unit: mm

Packaging	Pa	cking Methods		Ammo Packing						
Туре	Α	B1-B2	s	Α	В	С	Qty			
Carbon 0.125W	26+1/-0	1.0	5	80	105	264	5,000			
Carbon 0.25W	26+1/-0	1.0	5	80	105	264	5,000			
Carbon 0.5W (H)	26+1/-0	1.0	5	80	105	264	5,000			
Carbon 1W (H)	73+1/-0	1.5	5	103	82	265	1,000			
Carbon 2W (H)	73+1/-0	1.5	10	103	96	265	1,000			

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.



■Marking & Resistance Tolerance

ENGLISH



±5%	E-24	1.0	1.1	1.2	1.3	1.5	1.6	1.8	2.0	2.2	2.4	2.7	3.0	3.3	3.6	3.9	4.3	4.7	5.1	5.6	6.2	6.8	7.5	8.2	9.1

Cold	Digit	Multiplier	Toler	ance	
	-	-	-	-	
	-	10 ⁻²	-	-	
	-	10 ⁻¹	±5.0%	J	
	0	10°	-	-	
	1	10 ¹	-	-	
	2	10 ²	-	-	
	3	10 ³	10 ³ -		
	4	10 ⁴	-	-	
	5	10 ⁵	-	-	
	6	10 ⁶	-	-	
	7	10 ⁷	-	-	
	8	10 ⁸	-	-	
	9	10 ⁹	-	-	