



VeriSafe 1.0 AVT, 8' (2.4m) system cable, 10' (3m) sensor leads

VS-AVT-C08-L10

The VS-AVT-C08-L10 VeriSafe 1.0 Absence of Voltage Tester is a permanently mounted voltage tester for use in 3-phase AC systems up to 600 V. Activating VeriSafe performs an absence of voltage test before opening the panel, helping prevent possible exposure to electrical hazards, improving safety, and reducing downtime. This SKU includes a three-phase AVT tester equipped with 10' sensor leads, 8' system cable and an industrial lithium battery.

Specifications

Sub Brand	VeriSafe™
Product Type	Absence of Voltage Tester
Cable Length (ft.)	8
Cable Length (m)	2.44
Maximum Voltage (V ac)	600
Maximum Voltage (V dc)	600
Maximum Voltage (V)	600
Battery Voltage (V)	3.6
Standards Met	UL 1436, UL 508, CSA-C22.2 No. 14, CAN/CSA-C22 No.160, CAN/CSA-C22.2 No.107.1, IEC/UL/CSA C22.2 No. 61010-1, IEC/UL.CSA C22.2 No 61010-2-030, IEC 61508-1, -2 and -3 (SIL Rating)
Battery Type	Lithium-Ion
For Use With	3-Phase AC systems
Power Source	Lithium Battery
Network Compatible	No
Maximum Operating Temperature (°C)	60
Maximum Operating Temperature (°F)	140
Minimum Operating Temperature (°C)	-25
Minimum Operating Temperature (°F)	-13
Maximum Storage Temperature (°C)	85
Maximum Storage Temperature (°F)	185
Minimum Storage Temperature (°C)	-45
Minimum Storage Temperature (°F)	-49

Packaging Detail

UPC	61305625682
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.3177
Std. Ctn. Qty.	8
Std. Ctn. Volume (cf)	2.5418