

Eaton 13NZ01

Catalog Number: 13NZ01

Fuse-link, LV, 13 A, AC 400 V, D01, gL/gG, IEC, time-delay

General specifications



Product Name	Catalog Number
Eaton Bussmann series low voltage D0 fuse	13NZ01
	EAN
	5027590433501
Product Length/Depth	Product Height
36 mm	11 mm
Product Width	Product Weight
11 mm	6.6 g
Compliances	Certifications
CE Marked	IEC 60269
RoHS Compliant	EAC
	DIN EN 60269-3 (VDE 0636 Part 30)
	DIN EN 60269-1 (VDE 0636 Part 10)
	DIN VDE 0636-301

Product specifications

Type

Fuse

Application

For domestic and general industrial applications

Amperage Rating

3 A

Fuse size

D01

Breaking capacity

50 kA

Rated voltage AC

400 V

Class

Class C gL/gG

Fuse type

NZ01 - Time delay

Utilization category

gG (cable protection/equipment protection)

Color

Black

Interrupt rating

50 kAIC

Fuse indicator

Non-indicating

Connection

Other

Construction

D01

Construction size

D01

Fuse shape

Bottle

Response time

Time-delay

Suitable for

Resources

Brochures

[eaton-bussmann-series-d-and-d0-fuses-product-aid-pa132014en-en-us.pdf](#)

Catalogs

[CA134002EN](#)

Declarations of conformity

[UKCA Bottle fuse-links, holders, carriers and accessories](#)

[CE Bottle fuse-links, holders, carriers and accessories](#)

Technical service bulletins

[Datasheet - 13NZ01](#)

E14 (D01) Fuse base
FRN01C Single-pole fuse base
FN01C Single-pole fuse base
FRN01-B Single-pole fuse base
FRN01-SB Single-pole fuse base
TFRN01C Three-pole fuse base
TFN01C Three-pole fuse base
TFRN01-B Three-pole fuse base
TFRN01-SB Three-pole fuse base

Material

White ceramic body

Voltage rating

400 V



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia