



MATERIAL

Glass-fibre reinforced polyamide based (PA) SUPER-technopolymer, black colour, matte finish.

ROTATING PIN

AISI 303 stainless steel.

STANDARD EXECUTIONS






- **CFM-p**: nickel-plated steel threaded studs.
- **CFM-SH**: pass-through holes for countersunk head screws.
- **CFM-CH**: pass-through holes for cylindrical head screws with washer type UNI 6592.
- **CFM-p-SH**: nickel-plated steel threaded studs and pass-through holes for countersunk head screws.
- **CFM-p-CH**: nickel-plated steel threaded studs and pass-through holes for cylindrical head screws with UNI 6592 washer.

ROTATION ANGLE (APPROXIMATE VALUE)

Max 270° (-90° and +180° being 0° the condition where the two inter-connected surfaces are on the same plane).


Do not exceed the rotation angle limit so as not to prejudice the hinge mechanical performance.

To choose the convenient type and the right number of hinges for your application, see the Guidelines (see page 952).



Resistance tests	Axial Stress	Radial Stress	90° Angled Stress
Description	Max limit static load Sa [N]	Max limit static load Sr [N]	Max limit static load S90 [N]
CFM.30 SH-4	1400	1700	1000
CFM.30 CH-4	1300	1700	850
CFM.40 p-M5x12	2000	1900	1000
CFM.40 SH-5	1900	1900	1280
CFM.40 CH-5	1900	1600	1000
CFM.40 p-M5x12-SH-5	1900	1900	1000
CFM.40 p-M5x12-CH-5	1900	1600	1000
CFM.50 p-M6x12	2340	2560	2100
CFM.50 SH-6	2630	2400	1720
CFM.50 CH-6	2860	2410	1360
CFM.50 p-M6x12-SH-6	2340	2400	1720
CFM.50 p-M6x12-CH-6	2340	2410	1360
CFM.60 p-M8x14.5	3000	3940	2130
CFM.60 SH-6	3320	2960	3070
CFM.60 SH-8	3320	2960	3070
CFM.60 CH-8	3440	2810	2170
CFM.60 p-M8x14.5-SH-8	3000	2960	2130
CFM.60 p-M8x14.5-CH-8	3000	2810	2130

The max static load is the value beyond which the material may break thus prejudicing the hinge performance. Obviously, a suitable coefficient must be applied to this value, according to the importance and the safety level of the specific application.

**CFM-p**

Code	Description	L	B	d2	l	f1±0.25	f2±0.25	H	h1	h2	b1	b2	d	C# [Nm]	△
425521	CFM.40-p-M5x12	40	40	M5	12	25	25	9	5.5	5	14	14	4	5	26
425621	CFM.50-p-M6x12	50	50	M6	12	30	30	11.5	6.5	6	18	18	6	5	50
425721	CFM.60-p-M8x14.5	60	60	M8	14.5	36	36	15	8.5	8	21	21	8	5	101

CFM-SH

Code	Description	L	B	f1±0.25	f2±0.25	H	h1	h2	b1	b2	d	d3	d4	C# [Nm]	△
425411	CFM.30-SH-4	30	30	18	18	7	4	3.5	10.5	10.5	2.5	4.5	8.5	3	11
425511	CFM.40-SH-5	40	40	25	25	9	5.5	5	14	14	4	5.5	10.5	3	14
425611	CFM.50-SH-6	50	50	30	30	11.5	6.5	6	18	18	6	6.5	12.5	5	30
425710	CFM.60-SH-6	60	60	36	36	15	8.5	8	21	21	6	6.5	12.5	5	58
425711	CFM.60-SH-8	60	60	36	36	15	8.5	8	21	21	8	8.5	16.5	5	57

CFM-CH

Code	Description	L	B	f1±0.25	f2±0.25	H	h1	h2	h3	b1	b2	d	d3	d5	C# [Nm]	△
425412	CFM.30-CH-4	30	30	18	18	7	4	3.5	1.3	10.5	10.5	2.5	4.5	7.5	3	11
425512	CFM.40-CH-5	40	40	25	25	9	5.5	5	1.7	14	14	4	5.5	10.5	5	14
425612	CFM.50-CH-6	50	50	30	30	11.5	6.5	6	3	18	18	6	6.5	12.5	5	30
425712	CFM.60-CH-8	60	60	36	36	15	8.5	8	4	21	21	8	8.5	16.5	5	57

CFM-p-SH

Code	Description	L	B	d2	l	f1±0.25	f2±0.25	H	h1	h2	b1	b2	d	d3	d4	C [Nm] p#	C [Nm] SH#	△
425531	CFM.40-p-M5x12-SH-5	40	40	M5	12	25	25	9	5.5	5	14	14	4	5.5	10.5	5	3	20
425631	CFM.50-p-M6x12-SH-6	50	50	M6	12	30	30	11.5	6.5	6	18	18	6	6.5	12.5	5	5	40
425731	CFM.60-p-M8x14.5-SH-8	60	60	M8	14.5	36	36	15	8.5	8	21	21	8	8.5	16.5	5	5	79

CFM-p-CH

Code	Description	L	B	d2	l	f1±0.25	f2±0.25	H	h1	h2	h3	b1	b2	d	d3	d5	C [Nm] p#	C [Nm] CH#	△
425532	CFM.40-p-M5x12-CH-5	40	40	M5	12	25	25	9	5.5	5	1.7	14	14	4	5.5	10.5	5	5	20
425632	CFM.50-p-M6x12-CH-6	50	50	M6	12	30	30	11.5	6.5	6	3	18	18	6	6.5	12.5	5	5	40
425732	CFM.60-p-M8x14.5-CH-8	60	60	M8	14.5	36	36	15	8.5	8	4	21	21	8	8.5	16.5	5	5	79

Suggested tightening torque for assembly screws.