




Sensors > Safety Light Curtains



Safety Level: **Type 4 - PL e - Cat.4 , SIL3, SILCL3**

Detection Type: **Hand**

Detection Resolution: **30 mm**

Sensing Distance (Max): **12 mm**

Response Time: **5.5 msec**

Features

Configuration Features

Safety Output Type	2 OSSD Pairs (400mA)
Connections Type	M12 5-Pole Connector (Emitter) & M12 8-Pole Connector (Receiver)
Number of Safety Outputs	2
Safety Functions	Integrated

Electrical Characteristics

Power Supply Voltage	24 ± 20% VDC
Output Current (Max)	.4 A
Output Voltage	24 VDC

Body Features

Product Weight	849 g
----------------	-------

Dimensions

Overall Height	363 mm
Controlled Height	310 mm
Connection Cable Length (Max)	100 m
Product Depth	28 mm



Product Length	30 mm
----------------	-------

Product Height	363 mm
----------------	--------

Usage Conditions

Storage Temperature Range	-30 – 70 °C[-22 – 158 °F]
---------------------------	---------------------------

Operating Temperature Range	-20 – 55 °C[-4 – 131 °F]
-----------------------------	--------------------------

Detection Resolution	30 mm
----------------------	-------

Sensing Distance (Max)	12 mm
------------------------	-------

Operation/Application

Number of Beams	16
-----------------	----

Detection & Functioning System	Emitter & Receiver
--------------------------------	--------------------

Protected Height	310 mm
------------------	--------

Start & Restart Type	Automatic & Manual
----------------------	--------------------

Indicator Type	LED
----------------	-----

Detection Type	Hand
----------------	------

Response Time	5.5 msec
---------------	----------

Industry Standards

IP Rating	IP67
-----------	------

Safety Level	Type 4 - PL e - Cat.4 , SIL3, SILCL3
--------------	--------------------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Not Yet Reviewed
-----------------------------	------------------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---




Solder Process Capability	Not reviewed for solder process capability
---------------------------	--


Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

 TE Part # 1-2447912-0 SLC-FC15-M12-90-5P	 TE Part # 1-2447912-1 SLC-FC-M12-5P-CG9	 TE Part # 1-2447912-2 SLC-FC-M12-90-5P-CG9	 TE Part # 1-2447913-0 SLC-FC15-M12-90-8P
 TE Part # 1-2447913-1 SLC-FC-M12-8P-CG11	 TE Part # 1-2447913-2 SLC-FC-M12-90-8P-CG11	 TE Part # 1-2447913-3 SLC-FC-M12-8P-CG9	 TE Part # 1-2447913-4 SLC-FC-M12-90-8P-CG9
 TE Part # 1-2447915-0 SLC-FMC-CG11-197	 TE Part # 1-2447917-0 SLC-SLC-MP-136	 TE Part # 1-2447917-1 SLC-SLC-MP-144	 TE Part # 1-2447917-2 SLC-SLC-MP-151



Documents

Product Drawings

SLC4-H30-031

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2446038-3_B2.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2446038-3_B2.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2446038-3_B2.3d_igs.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Safety Light Curtains

English

Safety Products Training

English

Product Specifications

Manuals & User Guides

English



Manuals & User Guides

English

Agency Approvals

UL Report

English