

■ GEBERIT



Technical drawing of a T-joint showing dimensions: L (total height), Z (height of the vertical part), d (diameter of the vertical part), R_p (radius of the fillet), l (length of the horizontal part), and l_1 (length of the fillet).

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water $\leq 120\text{ }^{\circ}\text{C}$
- For saturated steam $\leq 120\text{ }^{\circ}\text{C}$
- For service water and process water
- For treated water
- For rainwater with a pH value ≥ 5.5

- For grey and black water with a pH value ≥ 5.5
- For extinguishing water (wet)
- For extinguishing water (wet/dry, dry)
- For sprinklers (wet)
- For chemicals and technical liquids
- For compressed air (oil purity class 0–3)
- For negative pressure
- For inert gases (e.g. nitrogen)
- For industrial gases (e.g. acetylene, shielding gases)
- For technical building systems, industry and shipbuilding

- Pressing indicator
- Leaky if unpressed
- Two fastening points
- Seal ring made of CIIR, black
- Pressing socket with transparent protection plug

Product material	CrNiMo steel 1.4401 (EN 10088)
------------------	--------------------------------

Art. no.	DN	d, ø mm	Rp "	arc °	L cm	L1 cm	I cm	I1 cm	z cm
33423	12 / 15	15	1/2	90	5	6.5	3.5	1.5	3
33425	15	18	1/2	90	5	6.5	3.5	1.5	3
33427	20	22	3/4	90	5.4	6.5	3.1	1.6	3.3