

# Product datasheet

Specifications



## "PanelSet S3X stainless 304L, Scotch Brite® finish, H600xW400xD200 mm."

Local distributor code:

398252683

NSYS3X6420T

EAN Code: 3606480155239

## Main

Range	Spacial
Product name	Spacial S3X
enclosure type	Multi-purpose
category	Compact enclosure
nominal height	600 mm
nominal width	400 mm
nominal depth	200 mm
product installation	Wall-mounting
Device composition	1 body 1 lock: door 1 door

## Complementary

Body type	Single piece body, cross-shaped structure Gutter shaped front rail
Door type	Glazed
Number of doors	Front face: 1 door(s)
Door opening side	Reversible (120 °)
Lock type	2 points lock, 3 mm double-bar
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Body and door: stainless steel 304L Lock: zamak Hinge: stainless steel Door: Securit glass
Surface finish	Body and door: Scotch-Brite® brushed Lock: chromium plated
Net weight	9.58 kg

## Environment

Standards	IEC 62208 UL CUL
Product certifications	CAN/CSA 22 UL 508 type A

<b>IP degree of protection</b>	IP66 conforming to IEC 60529
<b>IK degree of protection</b>	IK08 conforming to IEC 62262
<b>Environmental characteristic</b>	Specific hygiene Corrosive

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	22.000 cm
<b>Package 1 Width</b>	41.500 cm
<b>Package 1 Length</b>	61.500 cm
<b>Package 1 Weight</b>	8.974 kg
<b>Unit Type of Package 2</b>	PAM
<b>Number of Units in Package 2</b>	4
<b>Package 2 Height</b>	56.000 cm
<b>Package 2 Width</b>	100.000 cm
<b>Package 2 Length</b>	120.000 cm
<b>Package 2 Weight</b>	50.900 kg

## Logistical informations

<b>Country of origin</b>	BG
--------------------------	----

## Contractual warranty

<b>Warranty (in months)</b>	18
-----------------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Total lifecycle Carbon footprint	133 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	92 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	18 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0.4 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	24 kg CO2 eq.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

### Use Better



### Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
EU RoHS Directive	<a href="#">Compliant</a>
REACH Regulation	<a href="#">Free of Substances of Very High Concern above the threshold</a>

### Use Longer



### Lifetime extension

Repair	No
--------	----

### Use Again



### Repack and remanufacture

End of life manual availability	No need of specific recycling operations
Take-back	Nej

Technical Illustration

Dimensions

---



Offer Marketing Illustration

Product benefits / Features

---



-  High resistance to corrosion
-  Earthing studs included
-  Large choice of dimensions & accessories
-  Built to last
-  Easy to equip  
Easy to maintain
-  Easy & quick assembly