

Main

Product or component type	Communication card
Range compatibility	Altivar 61 Altivar 71 Altivar 61Q Altivar 71Q
Communication port protocol	Modbus TCP
Product specific application	For daisy chain mounting
Connector type	1 RJ45
Transmission rate	10 Mbps 100 Mbps
Physical interface	Ethernet 2
Web services	Altivar chart Altivar viewer Data editor E-mail Ethernet statistics FDR Agent IO Scanner Security

Complementary

Exchange mode	Half duplex and full duplex
Communication data link	LLC : IEEE 802.2 MAC : IEEE 802.3
Communication network type	IP conforming to RFC791
Communication transport type	UDP TCP conforming to RFC793 8 connections maximum
Concept	Transparent Ready class C20
Web server	Embedded
Communication service	Write single register (06) Write multiple registers (16) TFTP SNMP Read/Write multiple registers (23) Read input registers (04) Read holding registers (03) Read device identification (43) I/O scanning service can be inhibited I/O profile FTP Diagnostics (08) Communication monitoring can be inhibited, adjustable CiA 402 profile
Display type	Web server Graphic display terminal for reference received Graphic display terminal for control word received 1 LED for TX (transmission) 1 LED for STS (IP address) 1 LED for RX (reception) 1 LED for FLT (Ethernet fault) 1 LED for 10/100 Mbps (speed)
Product weight	0.3 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.