

40VMax Disc Cutter XGT®, CE003G

40V, 230 mm, 6 600 min⁻¹

CE003G is a cordless 40Vmax XGT Li-Ion battery powered disc cutter with a blade diameter of 230mm.

Feature and benefits: Active Feedback sensing Technology (AFT), Water supply kit can be connected, Electric brake & Lock-off button.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	6600 min ⁻¹
Max. Depth of Cut	88 mm
Bore Size (Arbor Diameter)	17 / 22,23 mm
Disc Diameter	230 mm
Electronic brake	✓
Vibration Level, Concrete Cutting	3,0 / ≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Concrete Cutting	1,5 m/s ²
Sound Power Level (L _{WA})	116 dB(A)
Sound Pressure Level (L _{pA})	105 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)

User benefits

- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Electric brake for maximum productivity and increased operator safety
- Lock-off button prevents accidental startup

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing