

FEATURES

- **High chemical resistance:** Ensures longevity and reliability in harsh chemical environments
- **Maximum operating pressure of 3000 kPa:** Suitable for high-pressure applications
- **Maximum operating temperature of 280 °C:** Can withstand high-temperature conditions
- **Rotary speed of 18 m/s:** Supports high-speed operations without compromising performance
- **12.5 mm section:** Provides a robust sealing solution for various applications
- **Conforms to ANSI-ESD S20.20:2021, BAM, FDA, RoHS:** Meets key industry standards for safety and compliance

RS PRO 8m Polytetrafluoroethylene Gland Packing, 12.5mm Section

RS Stock No: 606-547



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO gland packing is designed for sealing applications in industrial environments. Made from high-quality polytetrafluoroethylene, it offers excellent chemical resistance and durability, making it ideal for use in demanding conditions. Its primary benefit is providing reliable sealing performance under high pressure and temperature.

General Specifications

Maximum Operating Pressure	3000 kPa
Product Type	Gland & Valve Packing
Rotary Speed	18 m/s
Section	12.5 mm
Sub Type	Gland Packing

Mechanical Specifications

Length	8 m
Material	Polytetrafluoroethylene

Operation Environment Specifications

Maximum Operating Temperature	280 °C
-------------------------------	--------

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, BAM, FDA, RoHS
---------------------	--------------------------------------