




EMI & EMC Solutions > EMI Filters > Power Entry Modules > CORCOM CU SERIES MULTI-FUNCTION INLET FI



Filter Type: **Power Entry Module**
Input Voltage Selection: **None**
Filter Switch Type: **SPST**
Filter Shield Type: **Complete Shield**
Device Safety Features: **Shrouded Output**

[All CORCOM CU Series Multi-Function Inlet FI \(0\)](#)

Features

Product Type Features

Ground Choke Option	No
Level Of Filtering	Inductor & Capacitor
Filter Type	Power Entry Module
Filter Switch Type	SPST
Output Termination Type	.187" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 60320-1 C-14

Configuration Features

Fuse Options	None
--------------	------

Electrical Characteristics

Input Voltage Selection	None
Leakage Current (Max) (120VAC, 60Hz)	250 μ A
Leakage Current (Max) (250VAC, 50Hz)	400 μ A



Current Rating	10 A
Operating Voltage	250 VAC

Body Features

Filter Shield Type	Complete Shield
Product Orientation	Vertical

Mechanical Attachment

Panel Mount Feature Type	Flange
Product Mount Type	Panel Mount

Dimensions

Panel Thickness (Recommended)	.63 – 2.1 mm [.024 – .08 in]
-------------------------------	------------------------------

Operation/Application

Device Safety Features	Shrouded Output
------------------------	-----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # CAT-C8114-C8911
CORCOM CU SERIES MULTI-FUNCTION INLET FI

Also in the Series

Customers Also Bought

TE Part #2-320554-1
PIDG R 22-16 COMM 22-18 MIL 8

TE Part #320677
BUDGET R 22-16COMM 22-18MIL 2

TE Part #91525-1
CCII AMPLIMITE HDP-20 PIN SKT 26-22 ASSY

TE Part #2-332004-0
SMA JAM NUT, PASSIVATED

TE Part #745253-3
20 DF SOCKET PLTD

TE Part #T4032014031-000
M8.MLE.PNLFRONT.3POS.STR

TE Part #90800-1
PROCRIMPER TOOL & DIE

TE Part #770522-2
SL156 RECEPT AUNI/PHBZ L/P

TE Part #2-328527-1
TERMINAL,PG R 16-14 8

TE Part #TAD14141311-001
M12D4-MS-PVC TYPE B RED-0.5M

Documents

Product Drawings
10CUFF1=F8306
English



CAD Files

Customer View Model

ENG_CVM_CVM_2-1609114-5_B.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1609114-5_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1609114-5_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654001_Corcom_Product_Guide_CU_Series

English

Corcom Combined Selector Charts

English

1-1654250-1_CORCOM_EMI_RFI_QRG

English

CORCOM_CU_SERIES

English