



22MM METAL ROUND ACTUATOR: EMERGEN.-STOP
MUSHR.PUSHB. 40MM WITH RONIS KEY-OPER.SWITCH
LATCHING WITH KEY-OPER.SWITCH- UNLOCKING LOCK
NO 421 WITH HOLDER RED

Actuator:

Design of the operating mechanism		mushromm pushbutton, Ø 40 mm, with key-operated switch no. 421
Shape / of the activation element		round
Manner of function / of the activation element		<ul style="list-style-type: none"> • arresting lock • tentative
Outer diameter / of the activation element	mm	40
Material / of the activation element		plastic

Button:

Color / of the button		red
-----------------------	--	-----

Front ring:

Material / of the front ring		metal
Color / of the front ring		silver

General technical details:

Design of the product		Ø 40 mm, latching, with pull-to-unlatch mechanism
Number of control points		1
Number of indicator lights / installable		0
Number of switching positions		2

Switch position for key distraction		O
Product extension / optional / fluorescent materials		No
Product function / emergency-OFF function		Yes
Type of unlocking device		key unlatching
Resistance against shock • for devices without incandescent lamp / according to IEC 60068-2-27		<= 50g
Operating cycles / maximum	1/h	1,000
Resistance against vibration / according to IEC 60068-2-6		20 ... 200 Hz: 5g
Mechanical operating cycles as operating time / typical		300,000
Item designation • according to DIN 40719 extendable after IEC 204-2 / according to IEC 750 • according to DIN EN 61346-2		S S

Auxiliary Contacts:

Number of NC contacts / for auxiliary contact		0
Number of NO contacts / for auxiliary contact		0
Number of change-over switches / for auxiliary contact		0

Installation/mounting/dimensions:


Product component / front ring		Yes
Material / of the housing		metal
Type of mounting		front mounting
Installation width	mm	22
Shape / of the installation hole		round
Mounting diameter	mm	22
Height	mm	40
Width	mm	40
Depth	mm	78
Tightening torque / of the screws in the holder / maximum	N·m	1

Ambient conditions:

Ambient temperature • during the operating phase • during storage	°C °C	70 ... -25 -40 ... 80
Protection class IP		IP67
Climatic class / according to DIN EN ISO 6270-2		KTW24

Certificates/approvals:

General Product Approval[ROSTEST](#)**Test Certificates**[Manufacturer](#)**Shipping Approval**[ABS](#)[PRS](#)**other**[Manufacturer](#)**Further information:****Information- and Downloadcenter (Catalogs, Brochures,...)**<http://www.siemens.com/industrial-controls/catalogs>**Industry Mall (Online ordering system)**<http://www.siemens.com/industrial-controls/mall>**CAX-Online-Generator**<http://www.siemens.com/cax>**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**<http://support.automation.siemens.com/WW/view/en/3SB3500-1YA20/all>**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3SB3500-1YA20



last change:

Sep 6, 2010