




Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Wire Entry Seal Kit**
Operating Temperature (Max): **105 °C [221 °F]**
Number of Positions: **3**
Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Connector Seal & Plug Type	Wire Entry Seal Kit
----------------------------	---------------------

Configuration Features

Number of Positions	3
---------------------	---

Mechanical Attachment

Thread Size	15/16-20
-------------	----------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Packaging Features

Packaging Method	Individual
Packaging Quantity	1

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------






EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Dodecamethylcyclohexasiloxane (D6) (.5% in 27519830211) Decamethylcyclopentasiloxane (D5) (.5% in 27519830211) Octamethylcyclotetrasiloxane (D4) (.5% in 27519830211) Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 197889-1 ANVIL HOLDER	 TE Part # 213906-1 CPC PLUG ASSY,SRS 6,SZ 17-10	 TE Part # 213845-5 POWERBAND CONT ASSY,SILVER PLT	 TE Part # 356611-1 DIES POWERBAND CONT 8 AWG DIE SET
--	---	--	---



TE Part # 356611-2
DIES POWERBAND CONT 10 AWG
DIE SET



TE Part # 213902-3
CPC CABLE CLAMP KIT,LRG,SZ 17




TE Part # 213843-2
POWERBAND SKT ASY,8-10,STRIP



TE Part # 213919-2
CPC SEAL KIT,UNASSM,SZ 17-14



TE Part # 213845-6
PWRBND PIN ASY,GRD,14-12,STRIP



TE Part # 356612-1
DIES POWERBAND CONT 14-12
AWG DIE SET



TE Part # 213847-1
POWERBAND CONT ASSY,SILVER PLT




TE Part # 213847-2
POWERBAND SKT ASY,14-12,STRIP



TE Part # 213905-1
CPC PLUG ASSY,SERIES 5,SZ 17-3



TE Part # 213845-4
PWRBAND PIN ASY 14-12 L.P.



TE Part # 213900-1
CPC SEAL ASSY KIT,SRS 6,17-10



TE Part # 213920-2
CPC SEAL KIT,UNASSM,SZ 17-16



TE Part # 213810-1
CPC COUPLING RING SIZE 17



TE Part # 213841-2
POWERBAND PIN CNT



TE Part # 788188-2
CPC 17-3 PLUG ASY,REV SEX



TE Part # 81665-2
FLANGE GASKET CPC

Also in the Series | [AMP Circular Plastic Connectors](#)



Circular Power Connectors(423)



Connector Backshells(1)



Connector Caps & Covers(16)



Connector Seals & Cavity Plugs(35)




Connector Strain Relief(60)



Insertion & Extraction Tools(1)


Customers Also Bought




TE Part #929986-1
1,5MM SOCK CONTACT




TE Part #K1060542
Relay 26-55-710




TE Part #63623-1
RCPT AMVAR 250 FAST LIF 016BR



TE Part #213847-1
POWERBAND CONT ASSY,SILVER PLT



TE Part #788188-2
CPC 17-3 PLUG ASY,REV SEX




TE Part #81665-2
FLANGE GASKET CPC




TE Part #K1145355
Rotary Switch DS-221-RT1



TE Part #4-2176611-1
EP 2W (SS) 47R 5%



TE Part #213845-1
POWERBAND CONT ASSY,SILVER PLT



TE Part #K1162382
CIRRUS-FWD-MCU_Redesign 89-03-002

Documents

Product Drawings

CPC SEAL ASSY KIT,SRS 5,17-3

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_213899-1_C.2d_dxf.zip



English

Customer View Model

[ENG_CVM_213899-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_213899-1_C.3d_stp.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_213899-1_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_213899-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_213899-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMP Circular Connectors for Commercial Signal & Power Applications](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[CSA Certificate](#)

English

[CSA Certificate](#)

English