

Eaton 191862

Catalog Number: 191862

Eaton Moeller® series R9 operating shaft 320mm

General specifications



Product Name	Catalog Number
Eaton Moeller® series R9 Accessory	191862
Operating shaft	EAN
	4015081923830
Product Length/Depth	Product Height
200 mm	5 mm
Product Width	Product Weight
5 mm	0.08 kg
Compliances	
CE	

Product specifications

Type

Drive shaft

10.10 Temperature rise

Not applicable.

10.11 Short-circuit rating

Not applicable.

10.12 Electromagnetic compatibility

Not applicable.

10.13 Mechanical function

Not applicable.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be

Resources

Catalogs

[Eaton-industrial-switch-disconnectors-catalogue-ca008011en-en-gb.pdf](#)

Drawings

[eaton-rotary-switches-r9-operating-shaft-3d-drawing.eps](#)

Installation instructions

[IL008047ZU](#)

mCAD model

[DA-CS-sf320sh5x5](#)

[DA-CD-sf320sh5x5](#)

Wiring diagrams

[eaton-rotary-switches-r9-switch-disconnector-wiring-diagram.eps](#)

evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Ambient operating temperature - max

50 °C

Ambient operating temperature - min

-25 °C

Cross section height

5 mm

Cross section width

5 mm

Equipment heat dissipation, current-dependent P_{vid}

0 W

Heat dissipation capacity P_{diss}

0 W

Heat dissipation per pole, current-dependent P_{vid}

0 W

Rated operational current for specified heat dissipation (I_n)

0 A

Shaft length

200 mm

Static heat dissipation, non-current-dependent P_{vs}

0 W

Shaft diameter

5 x 5 mm



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia