


BZV01/Z0000/70 Datasheet

 [View Product Page](#)

Product Name // Vertical Power Entry Module 72.3mm C14
Cold Condition Inlet Integral Single Fused (PF0011) 6.3mm
Tab Termination Unfiltered Double Contact Switch Marked
I/O



BZV01/****/** } A = 59.7 With Filter
BZV02/****/** } A = 27.4 Without Filter
BZV15/****/** } A = 59.7 With Filter
BZV16/****/** } A = 37.9 Without Filter
Panel Thickness: 1.0, 1.5, 2.0, 3.0mm.

// Product Description:

- Vertical Power Entry Module 58.9mm/72.3mm
- C14 Cold Condition Inlet with integral fuseholder(s) depending on part code:
- Part codes prefixed BZV01, BZV02: PF0011 Single Fused Inlet
- Part codes prefixed BZV15, BZV16: PF0033 Twin Fused Inlet
- Choice of Termination depending on part code:
- Part codes prefixed BZV01, BZV15: 6.3mm Tab
- Part codes prefixed BZV02, BZV16: 2.8mm Tab
- Choice of mains filter depending on part code:
- Part codes containing /Z0000 are unfiltered
- Choice of mains filter options (part codes containing codes starting /A)
- Choice of many other options as specified by individual part code, including indicators, illuminated switches, switch markings, etc

// General Information:

Product Display Title:	Vertical Power Entry Module 58.9mm/72.3mm
Product Family:	IEC Connectors
Product Series:	Power Entry Modules
Current Max:	10A
Filter Type:	Unfiltered
Function:	C14 Inlets
Fuseholder Inlet Type:	Integral Single Fused
Iec Connector Components:	None
Iec Connector Mates With:	PF0011
Iec Filter Options:	Unfiltered
Iec Vertical Module Height:	72.3mm
Inlet Type:	C14 Cold Condition Inlet
Switch Type:	Double Contact Marked I/O
Voltage Max:	250V

// Product PDF Links

 [Power Entry Modules product data](#)

// Product 3D CAD Model Links

 [BZV01/Z0000/703D CAD Model](#)