

Rotary Hammer LXT®

DHR241

18V • SDS-PLUS • 20 mm • 2.0 J

Professional long-framed, three-mode rotary hammer

An efficient rotary hammer for SDS-PLUS bits with an anti-vibration handle. Suitable for impact and unstressed drilling, plus chipping. Speed range of 0 – 1 100 min⁻¹. Impact energy of 2.0 J and max. drilling capacity of 20 mm in concrete.



LXT

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Impact Energy	1,9 J
Optimum Drilling Diameter Range in Concrete	4 - 12 mm
Max. Drilling Diameter in Concrete	20 mm
Max. Drilling Diameter in Wood	26 mm
Max. Drilling Diameter in Steel	13 mm
Impacts per Minute (IPM)	0 - 4000 min ⁻¹
No load speed	0 - 1200 min ⁻¹
Drilling diameter with TCT core bit	54 mm
Adapted for SDS-PLUS bits	✓
Tool weight with battery	3,2 - 4,0 kg
Electronic brake	✓
Vibration Level, Hammer Drilling Into	15,1 m/s ²

User benefits

- 3-Mode operation for "Rotation Only", "Hammering with Rotation" or "Hammering Only" for multiple applications
- One touch sliding chuck enables quick and easy bit changes
- Reversing switch
- Ergonomic chassis design ensures a good working position.
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing