

THERMOMARK-RIBBON 64-WMSE RD - Ink ribbon



5145740

<https://www.phoenixcontact.com/gb/products/5145740>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Ink ribbon, length: 300 m, roll length: 300 m, width: 64 mm, color: red



Commercial data

| | |
|--------------------------------------|--------------------|
| Item number | 5145740 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BG1223 |
| Product key | BG1223 |
| Catalog page | Page 555 (CL-2009) |
| GTIN | 4046356160803 |
| Weight per piece (including packing) | 241.4 g |
| Weight per piece (excluding packing) | 212.6 g |
| Customs tariff number | 96121010 |
| Country of origin | JP |

THERMOMARK-RIBBON 64-WMSE RD - Ink ribbon



5145740

<https://www.phoenixcontact.com/gb/products/5145740>

Technical data

Product properties

| | |
|-------------------|------------|
| Product type | Ink ribbon |
| Scope of delivery | Ink ribbon |

Marking

| | |
|---------------------------|------------------|
| Identification technology | Thermal transfer |
|---------------------------|------------------|

Dimensions

| | |
|----------------|-------|
| Width | 64 mm |
| Length | 300 m |
| Length of roll | 300 m |

Material specifications

| | |
|----------|----------------|
| Color | red (RAL 3001) |
| Material | Polyester |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Recommended ambient temperature (storage/transport) | 5 °C ... 35 °C |
| Recommended humidity (storage/transport) | 30 % ... 80 % (Storage in a dry and dark place in the original packaging is recommended) |
| Shelf life | 12 months (see packaging date) |

THERMOMARK-RIBBON 64-WMSE RD - Ink ribbon



5145740

<https://www.phoenixcontact.com/gb/products/5145740>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19140614 |
|-------------|----------|

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001694 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 44103100 |
|-------------|----------|

Environmental product compliance

| | |
|---|---|
| EU RoHS | |
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |