



Main

Range of product	Harmony Relay
Product or component type	Solid state relay
Device short name	SSM1
Network number of phases	1 phase

Complementary

Mounting support	Symmetrical DIN rail
[In] rated current	30 A
Output voltage	24...280 V AC
[Uc] control circuit voltage	90...280 V AC
Contacts type and composition	1 NO
Tightening torque	0.6...0.7 N.m for input 1.36...1.7 N.m for output
Connections - terminals	Screw terminals: 1 x 0.2...1 x 5.3 mm ² , (AWG 24...AWG 10) for input Screw terminals: 1 x 0.2...1 x 5.3 mm ² , (AWG 24...AWG 10) for output
Capacitance unbalance	8 PF for input/output
Insulation resistance	1000 MOhm at 500 V DC
Local signalling	LED (green) for input status
Switching voltage	90 V AC turn-on 10 V AC turn-off
Input current limits	2...10 MA
Solid state output type	SCR output Zero voltage switching
Load current	0.15...30 A
Absolute maximum voltage	600 V
Surge current	250 A for 16.6 ms
Maximum voltage drop	<1.6 V on-state
Maximum I ² t for fusing	6000 A ² .S for 8.3 ms
Maximum leakage current	10 MA off-state
DV/dt	500 V/μs off-state at maximum voltage
Response time	10 ms (turn-on) 40 ms (turn-off)
Overvoltage category	III
Net weight	0.28 Kg

Environment

Dielectric strength	4 KV AC for input/output 4 KV AC for input or output to case
Pollution degree	2
Standards	UL 508 CSA C22.2 No 14 IEC 60950-1
Product certifications	CSA EAC UL
Marking	CE EAC UL CSA
IP degree of protection	IP20
Ambient air temperature for operation	-40...80 °C
Ambient air temperature for storage	-40...125 °C

Packing Units

Package 1 Weight	0.299 Kg
------------------	----------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Product Life Status : **Commercialised**