

MSA V-TEC® SRLs

Technical Datasheet



Available in lifeline materials of galvanized steel, stainless steel, or synthetic rope, **V-TEC Self-Retracting Lanyards (SRLs)** are intended to form a complete connecting element between the user's body harness and an overhead anchor.

Key Features

- The internal energy absorber reduces arresting forces and eliminates need for less durable webbing external energy absorber
- Made with corrosion resistant materials
- Retraction dampening device reduces lifeline retraction velocity preserving the life of the unit
- The toughened case is engineered to resist impact damage and protect internal components
- Clear case allows for visual inspection of device internal mechanisms.

Product Specifications

Material	
CASE	Polycarbonate
PAWLS	Hardened stainless steel
CHASSIS	Stainless steel
FASTENERS	Stainless steel
RETRACTION SPRING	Stainless steel
DRUM MODULE	Polycarbonate / ABS blend
LIFELINE	Galvanized steel, stainless steel, or synthetic rope
LOCKING MECHANISM	Stainless steel and manganese bronze core
CONNECTORS	Forged zinc-plated steel/stainless steel with load indicator



Technical Specifications		
	Cable	Synthetic Rope
LENGTH	6 m, 10 m, 15 m	7 m, 10 m, 15 m
LIFELINE TYPE	5mm galvanized or stainless steel cable (7x19)	5mm High Modulus Polyethylene
SIZE	6 m: 190 x 175 x 110 mm (HxWxD) 10 m: 220 x 115 x 220 mm (HxWxD) 15 m: 220 x 115 x 220 mm (HxWxD)	7 m: 220 x 115 x 220 mm (HxWxD) 10 m: 220 x 115 x 220 mm (HxWxD) 15 m: 220 x 115 x 220 mm (HxWxD)
NET WEIGHT	6 m: 4 kg 10 m: 7 kg 15 m: 7.6 kg	7 m: 6.2 kg 10 m: 6.4 kg 15 m: 6.6 kg
USER WEIGHT RANGE	60 – 140 kg including tools	60 – 140 kg including tools
TEMPERATURE RANGE	-40°C to 60°C -40°F to 140°F	-40°C to 60°C -40°F to 140°F
APPROVALS	EN 360	EN 360

WE KNOW WHAT'S AT STAKE.



Ordering Information

Part Number	Cable Length	Cable Type		
		Galvanized	Stainless	Synthetic
63206-00AEU	6 m	■		
63210-00AEU	10 m	■		
63215-00AEU	15 m	■		
63306-00AEU	6 m		■	
63310-00AEU	10 m		■	
63315-00AEU	15 m		■	
VTOHR-071-ME-E	7 m			■
VTOHR-101-ME-E	10 m			■
VTOHR-151-ME-E	15 m			■

Our Mission

MSA's mission is to see to it that men and women may work in safety and that they, their families, and their communities may live in health throughout the world.

MSA: WE KNOW WHAT'S AT STAKE.

Note: This Bulletin contains only a general description of the products shown. While product uses and performance capabilities are generally described, the products shall not, under any circumstances, be used by untrained or unqualified individuals. The products shall not be used until the product instructions/user manual, which contains detailed information concerning the proper use and care of the products, including any warnings or cautions, have been thoroughly read and understood. Specifications are subject to change without prior notice. MSA is a registered trademark of MSA Technology, LLC in the US, Europe, and other Countries. For all other trademarks visit <https://us.msasafety.com/Trademarks>.

MSA operates in over 40 countries worldwide. To find an MSA office near you, please visit [MSAsafety.com/offices](https://us.msasafety.com/offices).