

# LS-EMP-AL (27X15) BK - Device marker



0831669

<https://www.phoenixcontact.com/gb/products/0831669>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Device marker, Aluminum label, black, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, mounting type: latching, Number of individual labels: 40, text field height: 15 mm, text field width: 27 mm



## Your advantages

- Aluminum equipment marking for snapping into marker carriers
- Identification made from metal, high strength in a lightweight design
- Increased durability due to the decoratively anodized surface

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 0831669             |
| Packing unit                         | 5 pc                |
| Minimum order quantity               | 5 pc                |
| Sales key                            | BG241D              |
| Product key                          | BG241D              |
| Catalog page                         | Page 289 (C-3-2019) |
| GTIN                                 | 4046356926034       |
| Weight per piece (including packing) | 85 g                |
| Weight per piece (excluding packing) | 77.08 g             |
| Customs tariff number                | 76169990            |
| Country of origin                    | CN                  |

## Technical data

### Product properties

|              |                |
|--------------|----------------|
| Product type | Device marking |
| Type         | Laser sheet    |

### Marking

|                             |                      |
|-----------------------------|----------------------|
| Number of individual labels | 40                   |
| Identification technology   | Direct laser marking |

### Mounting

|               |          |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

### Material specifications

|                |                                          |
|----------------|------------------------------------------|
| RoHS compliant | yes                                      |
| Color          | black (RAL 9005)                         |
| Material       | Aluminum                                 |
| Components     | free from silicone, halogen, and cadmium |

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

#### Test for substances that would hinder coating with paint or varnish

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

#### Tesafilem test

|               |                                  |
|---------------|----------------------------------|
| Specification | DIN EN ISO 2409:2013 (following) |
| Result        | Test passed                      |

#### UV resistance

|               |                                |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result        | Test passed                    |
| Test duration | 96 h                           |

#### Weathering-resistance

|               |                    |
|---------------|--------------------|
| Specification | ISO 4892-2:2013-03 |
| Result        | Test passed        |
| Test duration | 1500 h             |
| Procedure     | A                  |

#### Temperature resistance

|                        |                                 |
|------------------------|---------------------------------|
| Specification          | ANSI/UL 969-2018:03 (following) |
| Test duration          | 240 h                           |
| Rating 150 °C (180 °C) | Test passed                     |

# LS-EMP-AL (27X15) BK - Device marker



0831669

<https://www.phoenixcontact.com/gb/products/0831669>

## Wipe resistance of inscriptions

|                                                   |                                                |
|---------------------------------------------------|------------------------------------------------|
| Specification                                     | DIN EN 61010-1 (VDE 0411-01):2020-03           |
|                                                   | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropyl<br>[CAS No. 67-63-0]                    | Test passed                                    |
| n-Hexane<br>[CAS No. 110-54-3]                    | Test passed                                    |
| Water + Petroleum ether<br>[CAS No. 64742-82-1]   | Test passed                                    |
| Sodium hydroxide 0.1 mol/l<br>[CAS No. 1310-73-2] | Test passed                                    |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed                                    |
| Acetone (99 %)<br>[CAS No. 67-64-1]               | Test passed                                    |
| Specification                                     | ISO 175:2010 (following)                       |
| Test duration                                     | 168 h                                          |
| Ethanol (99 %)<br>[CAS No. 64-17-5]               | Test passed                                    |
| Acetone (99 %)<br>[CAS No. 67-64-1]               | Test passed                                    |
| Diesel<br>[CAS No. 68476-34-6]                    | Test passed                                    |
| IRM 901                                           | Test passed                                    |
| IRM 902                                           | Test passed                                    |

## Testing in a condensation changing climate in the presence of sulfur dioxide

|               |                   |
|---------------|-------------------|
| Specification | DIN 50018:2013-05 |
| Result        | Test passed       |
| Climate level | AHT 1.0 S         |
| Cycles        | 2                 |

## Salt spray test

|               |                           |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result        | Test passed               |
| Test duration | 96 h                      |

## Salt spray test

|               |                  |
|---------------|------------------|
| Specification | ISO 9227:2012-05 |
| Result        | Test passed      |
| Test duration | 336 h            |

## High pressure test

|               |                   |
|---------------|-------------------|
| Specification | ISO 20653:2013-02 |
| Result        | Test passed       |

## Ambient conditions

|                                 |                                                                                                       |
|---------------------------------|-------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation) | -25 °C ... 70 °C (At temperatures above 80 °C there might be a slight change to the material surface) |
|---------------------------------|-------------------------------------------------------------------------------------------------------|

# LS-EMP-AL (27X15) BK - Device marker



0831669

<https://www.phoenixcontact.com/gb/products/0831669>

|                                                     |       |
|-----------------------------------------------------|-------|
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport)            | 50 %  |

## Dimensions

|                   |         |
|-------------------|---------|
| Width             | 27 mm   |
| Length            | 14.8 mm |
| Material strength | 0.80 mm |

## Text field

|                   |       |
|-------------------|-------|
| Text field width  | 27 mm |
| Text field height | 15 mm |

## Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

# LS-EMP-AL (27X15) BK - Device marker



0831669

<https://www.phoenixcontact.com/gb/products/0831669>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27281106 |
| ECLASS-12.0 | 27281106 |
| ECLASS-13.0 | 27281106 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001288 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131700 |
|-------------|----------|

# LS-EMP-AL (27X15) BK - Device marker



0831669

<https://www.phoenixcontact.com/gb/products/0831669>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)