



### Main

Network rated voltage	400 V AC 50 Hz 415 V AC 50 Hz
Reactive power rating	300 kvar
Operating mode	Automatic
Range	PowerLogic
Device short name	automatic capacitor bank
Product or component type	Capacitor bank





### Complementary

Network pollution level	No polluted
[Gh/Sn] harmonic pollution rate	0...15 %
[THDU] total harmonic distortion of voltage	0...3 %
Power per step	50 kvar
Step composition	6x50
Location of connection	Bottom
Controller type	PowerLogic PFC Controller VPL6
Capacitor technology	EasyLogic PFC Capacitor
Poles description	3P
Capacitance tolerance	- 5 % to 10 %
[Ui] rated insulation voltage	690 V
[Uimp] rated impulse withstand voltage	8 kV
Maximum permissible voltage	1.1 x Un (8 hours over 24 hours) conforming to IEC 60831
[Imp] maximum permanent current	Battery: 1.36 x In at 400 V conforming to IEC 61439-2 Battery: 1.19 x In at 415 V conforming to IEC 61439-2 Capacitor: 1.5 x In at 480 V conforming to IEC 60831
Main incomer protection	Without protection
[Icw] rated short-time withstand current	30 kA at 1 s (Icw)
Step protection type	Overload: harmonic control from PowerLogic PFC Controller Short-circuit: upstream protection
Accessibility for operation	Front
Colour	Grey (RAL 7035)
Maximum weight	140 kg
Height	1100 mm
Width	800 mm
Depth	400 mm
Provided equipment	Auxiliary transformer
Internal voltage transformer	400/230 V - 400 VA
Function available	GenSet shedding contact Alarm contact

## Environment

Standards	IEC 61921 IEC 61439-1 IEC 61439-2
Product certifications	ASEFA[RETURN]CE
Mounting location	Indoor
IP degree of protection	Environment: IP31
IK degree of protection	IK10
Relative humidity	0...95 %
Operating altitude	<= 2000 m
Ambient air temperature for operation	-5...45 °C
Average ambient air temperature for operation	35 °C (annual) 45 °C (over 24 hours)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins